



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Prod Compliance Engineer, China CIS Compliance		
Company Unique ID	TE Connectivity	Response Date	2017-01-31	Contact Email	cc.wu@te.com				
Contact Phone Number	86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640445-3	Amount	1081.9174	Version	-	Identity			
Manufacturer Item Name	03P MTA156 HDR ASSY FL/STR SN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Compound				1.0	542.9	mg	
Material	2	PBT-GF7				1.0	542.9	mg	
Substance	3	4,4'-isopropylidene diphenol (bisphenol A; BPA)	Supplier	80-05-7	0.01	1.0	0.05429	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	35.2885	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	162.87	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	43.432	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	5.429	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	295.82621	mg	
Sub-Item	1	Brass Square				1.0	539.0174	mg	
Material	2	Brass Wire				1.0	532.57278439	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	380.78954	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00532573	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	149.24074	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.26629	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00532573	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.26629	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.53257	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.05272471	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.05325728	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.26629	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.02662864	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00266286	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.06515	mg	
Material	2	Tin Plate				1.0	4.00217266	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00800434	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	3.99137	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00280152	mg	
Material	2	Nickel Plate				1.0	2.44244296	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00488489	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00244244	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.43512	mg	