





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L1	ECO-14-010907	09SEP2014	KR	OC



LEADER	71.12	[2.800]	28	5-641201-8
	68.58	[2.700]	27	5-641201-7
	66.04	[2.600]	26	5-641201-6
	63.50	[2.500]	25	5-641201-5
	60.96	[2.400]	24	5-641201-4
	58.42	[2.300]	23	5-641201-3
	55.88	[2.200]	22	5-641201-2
	53.34	[2.100]	21	5-641201-1
	50.80	[2.000]	20	5-641201-0
	48.26	[1.900]	19	4-641201-9
	45.72	[1.800]	18	4-641201-8
	43.18	[1.700]	17	4-641201-7
	40.64	[1.600]	16	4-641201-6
	38.10	[1.500]	15	4-641201-5
	35.56	[1.400]	14	4-641201-4
	33.02	[1.300]	13	4-641201-3
	30.48	[1.200]	12	4-641201-2
	27.94	[1.100]	11	4-641201-1
	25.40	[1.000]	10	4-641201-0
	22.86	[.900]	9	3-641201-9
	20.32	[.800]	8	3-641201-8
	17.78	[.700]	7	3-641201-7
	15.24	[.600]	6	3-641201-6
	12.70	[.500]	5	3-641201-5
	10.16	[.400]	4	3-641201-4
	7.62	[.300]	3	3-641201-3
5.08	[.200]	2	3-641201-2	
	DIM A	NO.OF POSN	ASSEMBLY	

CONTOUR S L E A D	71.12	[2.800]	28	2-641201-8	△
	68.58	[2.700]	27	2-641201-7	△
	66.04	[2.600]	26	2-641201-6	△
	63.50	[2.500]	25	2-641201-5	△
	60.96	[2.400]	24	2-641201-4	△
	58.42	[2.300]	23	2-641201-3	△
	55.88	[2.200]	22	2-641201-2	△
	53.34	[2.100]	21	2-641201-1	△
	50.80	[2.000]	20	2-641201-0	△
	48.26	[1.900]	19	1-641201-9	△
	45.72	[1.800]	18	1-641201-8	△
	43.18	[1.700]	17	1-641201-7	△
	40.64	[1.600]	16	1-641201-6	△
	38.10	[1.500]	15	1-641201-5	△
	35.56	[1.400]	14	1-641201-4	△
	33.02	[1.300]	13	1-641201-3	△
	30.48	[1.200]	12	1-641201-2	△
	27.94	[1.100]	11	1-641201-1	△
	25.40	[1.000]	10	1-641201-0	△
	22.86	[.900]	9	641201-9	△
	20.32	[.800]	8	641201-8	
	17.78	[.700]	7	641201-7	△
	15.24	[.600]	6	641201-6	△
	12.70	[.500]	5	641201-5	
10.16	[.400]	4	641201-4		
7.62	[.300]	3	641201-3	△	
5.08	[.200]	2	641201-2	△	
	DIM A		NO.OF POSN	ASSEMBLY	

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOPER 20-DEC-2004 CHK D. BOSSI 20-DEC-2004		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: APD D. BOSSI 20-DEC-2004		NAME	
		PRODUCT SPEC 108-1050		MTA .100 CONNECTOR ASSEMBLY, 26 AWG, STANDARD	
0 PLC ± 1 PLC ± 2 PLC ± 0.13 [.005] 3 PLC ± 4 PLC ± ANGLES FINISH ±		APPLICATION SPEC 114-1019		SIZE GAGE CODE DRAWING NO A1 00779 C-641201	
MATERIAL 		WEIGHT 		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1 REV L	