



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Prod Compliance Engineer, China CIS Compliance		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-27	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	+86-21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-641208-3	<b>Amount</b>	1121.9243	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	03P MTA156 HDR ASSY FL ST LF	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Polyester Compound				1.0	542.9	mg	
Material	2	PBT-GF7				1.0	542.9	mg	
Substance	3	4,4'-isopropylidene diphenol (bisphenol A; BPA)	Supplier	80-05-7	0.01	1.0	0.05429	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	35.2885	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	162.87	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	43.432	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	5.429	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	295.82621	mg	
Sub-Item	1	MTA156 BAND/PIN ASSY AU .650 PDNI				3.0	193.0081	mg	
Material	2	Tin Plate				3.0	0.673	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001346	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.67118	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	4.711E-4	mg	
Material	2	Gold Plate				3.0	0.0565	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	3.0	0.055935	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	3.0	5.65E-4	mg	
Material	2	Palladium-Nickel Plate				3.0	0.3196	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	3.0	0.25568	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	3.0	0.06392	mg	
Material	2	Nickel Plate				3.0	0.854	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001708	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	8.54E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.85144	mg	
Material	2	Brass Wire				3.0	191.105	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	136.64007	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.00191105	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	3.0	53.55259	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.0955525	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	0.00191105	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.0955525	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.1911	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	3.0	0.01891939	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.0191105	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.0955525	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.00955525	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	9.5553E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.38221	mg	