



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
<b>Supplier Information</b>									
Company Name	TE Connectivity	Request Document ID		Contact Name	Chan, Nelson	Contact Title	Manager Sales, HKG SELL DIR-EMS		
Company Unique ID	TE Connectivity	Response Date	2016-11-11	Contact Email	nelson.chan@te.com				
Contact Phone Number	852-2738-8751								
<b>Legal Statement</b>									
Supplier Acceptance	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
Manufacturer Item number	640903-1	Amount	1583.46988	Version	-	Identity			
Manufacturer Item Name	RECEPT, PIDG FASTON 22-18 250	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Manufacturing Information</b>									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Not Applicable		
Preheat Duration		bulk Solder Termination	Not Applicable	Nbr or Reflow Cycles		Terminal Plating	Not Applicable		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	Not Applicable		
<b>Product Disclosure</b>									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	RECEPT, PIDG FASTON 22-18 250				1.0	1583.46988	mg	
Material	2	Copper				1.0	571.43	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.28572	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0057143	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	570.04428	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0057143	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0285715	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.057143	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.11429	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.57143	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.28572	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00285715	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0285715	mg	
Material	2	PA66				1.0	78.5272824	mg	
Substance	3	Phosphoric acid	Supplier	7664-38-2	0.075	1.0	0.05889546	mg	
Substance	3	Acetic acid	Supplier	64-19-7	0.015	1.0	0.01177909	mg	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	89.39	1.0	70.19554	mg	

Substance	3	Acetic acid, copper(2) salt (2:1)	Supplier	142-71-2	0.02	1.0	0.01570546	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	7.85273	mg	
Substance	3	Potassium bromide	Supplier	7758-02-3	0.5	1.0	0.39264	mg	
Material	2	Tin Plate				1.0	17.41	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	17.36299	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.03482	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.012187	mg	
Material	2	Brass				1.0	914.5	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.009145	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	256.26576	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.45725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.09145	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.45725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.9145	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	653.8675	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.009145	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.09145	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0045725	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.829	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.045725	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.45725	mg	
Material	2	COLORANT				1.0	1.6025976	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	0.01442338	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	96.4	1.0	1.5449	mg	
Substance	3	9,10-Anthracenedione, 1-(methylamino)-	Supplier	82-38-2	2.7	1.0	0.04327014	mg	