



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	CC WU	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-05-28	Contact Email	cc.wu@tycoelectronics.com				
Contact Phone Number	021-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	643813-5	Amount	0.92303	Version	-	Identity			
Manufacturer Item Name	05P MTA100 CONN ASSY POL RIB	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MTA100 CONT 22AWG SNPB/PHBZ				5.0	0.092706	g	
Material	2	Phos Bronze				5.0	0.0904	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	1.808E-5	g	
Substance	3	Copper	Supplier	7440-50-8	93.1335	5.0	0.08419268	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	5.0	2.712E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	5.0	9.04E-6	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	5.0	3.164E-4	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	5.0	9.04E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	5.0	1.356E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	5.0	9.04E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	9.04E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	9.04E-6	g	
Substance	3	Tin	Supplier	7440-31-5	5.8	5.0	0.0052432	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	9.04E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	4.52E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	5.0	4.52E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	5.0	9.04E-5	g	
Material	2	Tin-Lead Plate				5.0	0.002306	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	5.0	1.6142E-4	g	
Substance	3	Tin	Supplier	7440-31-5	92.3	5.0	0.00212844	g	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	5.0	1.6142E-5	g	
Sub-Item	1	5P MTA100 HSG 24AWG WHITE				1.0	0.4595	g	
Material	2	COLORANT				1.0	0.00919	g	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	0.00135644	g	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	9.19E-5	g	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	84.24	1.0	0.00774166	g	
Material	2	PA66				1.0	0.45031	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	99.355	1.0	0.4474055	g	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	9.0062E-6	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediy]bis-	Supplier	110-30-5	0.3	1.0	0.00135093	g	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	9.0062E-4	g	
Substance	3	Aluminum, hydroxybis(octadecanoato-kappa.O)-	Supplier	300-92-5	0.14	1.0	6.3043E-4	g	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	1.35093E-5	g	