



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2016-04-11	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	787928-7	Amount	14906.7952494	Version	-	Identity			
Manufacturer Item Name	68 50SR R/A RECPT,REDESIGN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	68 50SR R/A PIN SPACER				1.0	661.5	mg	
Material	2	PPA-GF33				1.0	661.5	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	23.3	1.0	154.1295	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	9.9225	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.2	1.0	232.848	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.9	1.0	25.7985	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.3	1.0	1.9845	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	34.5	1.0	228.2175	mg	
Substance	3	Calcium oxide (CaO)	Supplier	1305-78-8	0.4	1.0	2.646	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	5.9535	mg	
Sub-Item	1	BOARDLOCK, STRIP, PLATED				2.0	136.3	mg	
Material	2	Brass				2.0	127.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.001277	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	35.78473	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.06385	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01277	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.06385	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.1277	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	91.3055	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.001277	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.01277	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	6.385E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.2554	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.006385	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.06385	mg	
Material	2	Tin-Lead Plate				2.0	5.4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	2.0	0.702	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	2.0	4.671	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	2.0	0.027	mg	
Material	2	Nickel Plate				2.0	3.2	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.0064	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.0032	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	3.1904	mg	
Sub-Item	1	68 50SR BD RCPT SHELL,PLTD,L P				1.0	1186.2	mg	
Material	2	Nickel Plate				1.0	95.3	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0953	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	95.0141	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.1906	mg	
Material	2	Copper Plate				1.0	23.9	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0239	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	23.8761	mg	
Material	2	Carbon Steel				1.0	1067.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	0.8536	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01067	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.5	1.0	5.335	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1067	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.2	1.0	2.134	mg	
Substance	3	Iron	Supplier	7439-89-6	98.8875	1.0	1055.12963	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.025	1.0	0.26675	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.025	1.0	0.26675	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01067	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1067	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.067	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.5335	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1067	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.067	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.005335	mg	
Sub-Item	1	68 50SR BRKT RTA RCPT,PLTD				1.0	6566.146935	mg	
Material	2	Zinc Alloy				1.0	6442.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	1.0	5.1536	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	2.2547	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.6442	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.06442	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	1.0	0.12884	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	3.221	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	1.2884	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	6.442	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	6.442	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	3.221	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.6442	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	1.0	6133.71809	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	277.006	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	1.2884	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	1.0	0.19326	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.03221	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	1.0	0.25768	mg	
Material	2	Nickel Plate				1.0	41.320478	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.04132048	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	41.19652	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.08264096	mg	
Material	2	Copper Plate				1.0	82.826457	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.08282646	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	82.74363	mg	
Sub-Item	1	50SR RT ANGLE CONT,PAIR,P LTD				34.0	145.1278916	mg	
Material	2	Tin-Lead Plate				34.0	1.201204	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	34.0	0.15616	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	34.0	1.03904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	34.0	0.00600602	mg	
Material	2	Phos Bronze				34.0	142.325721	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	34.0	134.78032	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	0.02846514	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	0.01423257	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	34.0	6.40466	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	34.0	0.00711629	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	34.0	0.14233	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	0.01423257	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	0.00142326	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	34.0	0.42698	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	34.0	0.14233	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	0.14233	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	34.0	0.00711629	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	34.0	0.07116286	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	0.14233	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	7.1163E-4	mg	
Material	2	Nickel Plate				34.0	1.594084	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	34.0	0.00318817	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	0.00159408	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	1.5893	mg	
Material	2	Gold Plate				34.0	0.0068826	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	0.00686195	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	34.0	2.06478E-5	mg	
Sub-Item	1	68 50SR R/A RCPT HSG				1.0	1286.0	mg	
Material	2	PPA-GF33				1.0	1286.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	23.3	1.0	299.638	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	19.29	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.2	1.0	452.672	mg	
Substance	3	Antimonate (SbO3 ¹⁻), sodium (1:1)	Supplier	15432-85-6	3.9	1.0	50.154	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.3	1.0	3.858	mg	

Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	34.5	1.0	443.67	mg	
Substance	3	Calcium oxide (CaO)	Supplier	1305-78-8	0.4	1.0	5.144	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	11.574	mg	