



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Manager Environmental Engineering		
Company Unique ID	TE Connectivity	Response Date	2015-07-01	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-1437667-9	Amount	17214.876396	Version	-	Identity			
Manufacturer Item Name	4DB-P108-06=4DB ASSEMBLY	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	511611070=6/32 W/C COMBO FOR 4				6.0	1479.669066	mg	
Material	2	Carbon Steel				6.0	995.569066	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	6.0	0.39823	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.09955691	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	6.0	978.13167	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.09955691	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.99557	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	6.0	0.49778	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00995569	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	6.0	2.28981	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	6.0	1.49335	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	6.0	9.95569	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.09955691	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.00497784	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.99557	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	6.0	0.49778	mg	
Material	2	Tri Chrome Film				6.0	2.077	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	6.0	1.2462	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	6.0	0.6231	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	6.0	0.2077	mg	
Material	2	Carbon Steel				6.0	482.023	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	6.0	0.72303	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.0482023	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	6.0	0.24101	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00482023	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.9	6.0	4.33821	mg	
Substance	3	Iron	Supplier	7439-89-6	98.0285	6.0	472.51992	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	6.0	0.19281	mg	

Substance	3	Carbon	Supplier	7440-44-0	0.55	6.0	2.65113	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0482023	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.48202	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.00241012	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.0482023	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	6.0	0.24101	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.48202	mg	
Sub-Item	1	4DB-06,300V INSULATOR				1.0	3605.4	mg	
Material	2	COLORANT				1.0	180.27	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	1.8027	mg	
Substance	3	Carbon black	Supplier	1333-86-4	6.0	1.0	10.8162	mg	
Substance	3	C.I. Solvent Black 7	Supplier	8005-02-5	4.0	1.0	7.2108	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	89.0	1.0	160.4403	mg	
Material	2	PA66-FR				1.0	3425.13	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	95.0	1.0	3253.8735	mg	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	5.0	1.0	171.2565	mg	
Sub-Item	1	811262004=4D B-PC PLATED				6.0	788.577	mg	
Material	2	Brass				6.0	775.411	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	0.00775411	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	6.0	217.28955	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.38771	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0775411	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.38771	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.77541	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	6.0	554.41886	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00775411	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.0775411	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	0.00387705	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	1.55082	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	0.03877055	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.38771	mg	
Material	2	Tin Plate				6.0	10.088	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.010088	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	6.0	0.040352	mg	
Substance	3	Tin	Supplier	7440-31-5	99.5	6.0	10.03756	mg	
Material	2	Nickel Plate				6.0	3.078	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.006156	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	0.003078	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	3.06877	mg	