



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-19	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	+1-717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	87224-2	<b>Amount</b>	139.370883	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	02 MODII HDR SRST UNSHRD .100	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Nylon Compound				1.0	29.090883	mg	
Material	2	PA66-GF25				1.0	29.090883	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	23.95	1.0	6.96727	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	0.945	1.0	0.27491	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0020	1.0	5.8182E-4	mg	
Substance	3	1,4:7,10-Dimethanodibenzocyclooctene, 1,2,3,4,7,8,9,10,13,13,14,14-dodecachloro-1,4,4a,5,6,6a,7,10,10a,11,12,12a-dodecahydro-	Supplier	13560-89-9	14.17	1.0	4.12218	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	51.993	1.0	15.12522	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diundecyl ester, branched and linear	Supplier	85507-79-5	1.43	1.0	0.416	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.49	1.0	0.14255	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	2.1	1.0	0.61091	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.81	1.0	1.39927	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-kappa.O)-	Supplier	300-92-5	0.1	1.0	0.02909088	mg	
Substance	3	Copper iodide (CuI)	Supplier	7681-65-4	0.01	1.0	0.00290909	mg	

Sub-Item	1	MODII POST PLTD 15 AU				2.0	55.14	mg	
Material	2	Gold Plate				2.0	0.135	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	2.0	0.13459	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	2.0	4.05E-4	mg	
Material	2	Gold Plate				2.0	0.017	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	2.0	1.7E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	2.0	0.016983	mg	
Material	2	Phos Bronze				2.0	54.392	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	2.0	51.50841	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0108784	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0054392	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	2.0	2.44764	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.0027196	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.054392	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0054392	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	5.4392E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	0.16318	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	2.0	0.054392	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.054392	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0027196	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.027196	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.054392	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	2.7196E-4	mg	
Material	2	Nickel Plate				2.0	0.596	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001192	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	5.96E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.59421	mg	