



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	JASON KUNTZ	Contact Title	Product Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-04-17	Contact Email	jp.kuntz@te.com																													
Contact Phone Number		717-986-5932																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	9-215079-0	Amount	843.48	Version	-	Identity																												
Manufacturer Item Name	MICRO-MATCH FOB.20P	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	MICRO-MATCH FOB.CNT				20.0	19.474	mg																										
Material	2	Tin Plate				20.0	0.498	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	20.0	4.975E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	20.0	0.4975	mg																										
Material	2	Nickel Plate				20.0	0.076	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	1.52E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	7.6E-5	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	0.075772	mg																										
Material	2	Phos Bronze				20.0	18.9	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6835	20.0	17.89518	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	20.0	0.00378	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	20.0	0.00189	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	20.0	0.8505	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	20.0	0.002835	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.00189	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	20.0	0.0189	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	1.89E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	20.0	0.0567	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	20.0	0.0189	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	0.0189	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	20.0	0.00189	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	20.0	0.00945	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	20.0	0.0189	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	9.45E-5	mg																										
Sub-Item	1	MICRO-MATCH F HSG.L				1.0	454.0	mg																										
Material	2	PBT-GF20				1.0	454.0	mg																										
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	63.4	1.0	287.836	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.9	1.0	4.086	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.1	1.0	0.454	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	90.8	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.454	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.5	1.0	20.43	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	11.0	1.0	49.94	mg	