



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com																													
Contact Phone Number		1-717-592-4423																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-104549-6	Amount	2289.9317856	Version	-	Identity																												
Manufacturer Item Name	40 SYS50 S/M HDR DRST SHRDSN	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	40 SYSTEM 50 SURFMNT HDR HSG				1.0	1300.0	mg																										
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1300.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	39.0	mg																										
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	871.0	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	390.0	mg																										
Sub-Item	1	SYSTEM 50 SFMNT HLDWN PLTD SN				2.0	24.681288	mg																										
Material	2	Beryllium Copper				2.0	23.8815	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	0.47763	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.00238815	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0047763	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.047763	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.047763	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.095526	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00238815	mg																										
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.047763	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	2.3881E-4	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.649	2.0	23.08123	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.0238815	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.047763	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00119408	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.1941E-4	mg																										
Material	2	Tin Plate				2.0	0.537418	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	2.0	5.3688E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.9001	2.0	0.53688	mg																										
Material	2	Nickel Plate				2.0	0.26237	mg																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	5.2474E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.6237E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.26158	mg	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				40.0	23.51423024	mg	
Material	2	Gold Plate				40.0	0.0602	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.0600194	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	1.806E-4	mg	
Material	2	Tin Plate				40.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	40.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	40.0	0.07452547	mg	
Material	2	Brass				40.0	23.24	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	40.0	0.02324	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	40.0	14.8736	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	40.0	0.01162	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.324E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	40.0	0.002324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.02324	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	40.0	0.02324	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	40.0	8.18246	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.002324	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.002324	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	40.0	0.01162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	40.0	0.06972	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.002324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.162E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.01162	mg	
Material	2	Nickel Plate				40.0	0.137	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	2.74E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	1.37E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.13659	mg	
Material	2	Gold Plate				40.0	0.00243024	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.00242295	mg	