



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2017-02-15	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1734099-6	Amount	4943.076413	Version	-	Identity			
Manufacturer Item Name	Champ 050 series,plug assembly	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	60 50SR CHAMP TINEPLATE,S ER I				1.0	690.05581	mg	
Material	2	LCP-GF30				1.0	690.05581	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	20.70167	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	1.38011	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	13.80112	mg	
Substance	3	2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarb oxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoi c acid	Supplier	126710-21-2	65.8	1.0	454.05672	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	200.11618	mg	
Sub-Item	1	CHAMP VERT SER I RET LEG PLTD				2.0	95.221708	mg	
Material	2	Nickel Plate				2.0	0.642	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001284	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.42E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.64007	mg	
Material	2	Brass				2.0	93.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	9.3E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	26.06093	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.0465	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0093	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.0465	mg	

Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.093	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	9.3E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	66.495	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0093	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.65E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.186	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0465	mg	
Material	2	Tin Plate				2.0	1.579708	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00315942	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	1.57544	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.0011058	mg	
Sub-Item	1	50SR CHAMP R/A PLUG CONT				60.0	30.764688	mg	
Material	2	Phos Bronze				60.0	29.3	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	60.0	0.0293	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	60.0	0.00293	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	60.0	0.0586	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	60.0	0.001465	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	60.0	26.38421	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	60.0	0.10255	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	60.0	0.00586	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	60.0	2.93E-4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	60.0	0.00293	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	60.0	0.0293	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	60.0	2.637	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	60.0	0.0293	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	60.0	1.465E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	60.0	0.001465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	60.0	0.01465	mg	
Material	2	Nickel Plate				60.0	0.6727	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	60.0	0.0013454	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	60.0	6.727E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	60.0	0.67068	mg	
Material	2	Tin Plate				60.0	0.753	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	60.0	0.001506	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	60.0	0.75097	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	60.0	5.271E-4	mg	
Material	2	Palladium-Nickel Plate				60.0	0.015048	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	60.0	0.0120384	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	60.0	0.0030096	mg	
Material	2	Gold Plate				60.0	0.02394	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	60.0	0.0237006	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	60.0	2.394E-4	mg	
Sub-Item	1	60 50SR CHAMP R/A PLUG HSG				1.0	2216.695907	mg	
Material	2	LCP-GF30				1.0	2216.695907	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	66.50088	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	4.43339	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	44.33392	mg	

Substance	3	2,6-Naphthalenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoic acid	Supplier	126710-21-2	65.8	1.0	1458.58591	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	642.84181	mg	