



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Olson, Joseph R	<b>Contact Title</b>	Prod Sustaining Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-24	<b>Contact Email</b>	jrolson@te.com				
<b>Contact Phone Number</b>	1-717-592-4423								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-147377-5	<b>Amount</b>	3201.841512	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	50 SYS50 SMT HDR DR SHD SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	Brass				1.0	1162.0	mg	
Substance	2	Tin	Supplier	7440-31-5	0.1	1.0	1.162	mg	
Substance	2	Copper	Supplier	7440-50-8	64.0	1.0	743.68	mg	
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.581	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01162	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1162	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	1.162	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.1	1.0	1.162	mg	
Substance	2	Zinc	Supplier	7440-66-6	35.2085	1.0	409.12277	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.1162	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.1162	mg	
Substance	2	Aluminum	Supplier	7429-90-5	0.05	1.0	0.581	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.3	1.0	3.486	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1162	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00581	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.581	mg	
Material	1	Tin Plate				1.0	3.73	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.00372627	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9001	1.0	3.72627	mg	
Material	1	LIQUID CRYSTAL PLOYMER				1.0	1858.3	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	55.749	mg	
Substance	2	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	1245.061	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	557.49	mg	
Material	1	Aluminum Alloy				1.0	167.83	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.1	1.0	0.16783	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.05	1.0	0.083915	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.35	1.0	0.58741	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.05	1.0	0.083915	mg	
Substance	2	Iron	Supplier	7439-89-6	0.4	1.0	0.67132	mg	

Substance	2	Silicon	Supplier	7440-21-3	0.25	1.0	0.41958	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.05	1.0	0.083915	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.05	1.0	0.083915	mg	
Substance	2	Aluminium	Supplier	7429-90-5	95.5945	1.0	160.43625	mg	
Substance	2	Copper	Supplier	7440-50-8	0.1	1.0	0.16783	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.1	1.0	0.16783	mg	
Substance	2	Magnesium	Supplier	7439-95-4	2.8	1.0	4.69924	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.05	1.0	0.083915	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	8.3915E-4	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.083915	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0083915	mg	
Material	1	Gold Plate				1.0	3.01	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	3.00097	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.00903	mg	
Material	1	Nickel Plate				1.0	6.85	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0137	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00685	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	6.82945	mg	
Material	1	Gold Plate				1.0	0.121512	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	3.6454E-4	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.12115	mg	