



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A																									
<b>Supplier Information</b>																																		
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer David W	<b>Contact Title</b>	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD																											
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-03-22	<b>Contact Email</b>	dave.benfer@te.com																													
<b>Contact Phone Number</b>		+1-717-986-3725																																
<b>Legal Statement</b>																																		
<b>Supplier Acceptance</b>	true																																	
<b>Legal Statement</b>																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
<b>Product</b>																																		
<b>Manufacturer Item number</b>	1053635-1	<b>Amount</b>	4774.67661282	<b>Version</b>	-	<b>Identity</b>																												
<b>Manufacturer Item Name</b>	2081 0000 02	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>																												
<b>Date</b>		<b>UOM</b>	Each																															
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirements by application of the selected exemption(s)																																	
<b>ChinaRoHS-0508</b>	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
<b>EUREACH-0616</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
<b>Product Disclosure</b>																																		
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>																									
Sub-Item	1	3000 26 0154,GASKET				2.0	1.0	mg																										
Material	2	SILICONE				2.0	1.0	mg																										
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	14.75	2.0	0.1475	mg																										
Substance	3	Siloxanes and Silicones, di-Me, hydrogen-terminated, reaction products with epichlorohydrin formaldehyde-phenol polymer and [(2-propenyloxy)methyl]oxirane	Supplier	218163-11-2	70.0	2.0	0.7	mg																										
Substance	3	Silica gel, pptd., cryst.-free	Supplier	112926-00-8	10.25	2.0	0.1025	mg																										
Substance	3	Iron oxide (Fe2O3)	Supplier	1309-37-1	5.0	2.0	0.05	mg																										
Sub-Item	1	DIELECTRIC, SLIP/PRESS				1.0	407.6	mg																										
Material	2	Teflon				1.0	407.6	mg																										
Substance	3	1-Propene, 1,1,2,3,3,3-hexafluoro-polymer with 1,1,2,2-tetrafluoroethene	Supplier	25067-11-2	100.0	1.0	407.6	mg																										
Sub-Item	1	3000 28 0154,RETAINING RING, E				2.0	87.5	mg																										
Material	2	Beryllium Copper				2.0	87.5	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	8.75E-4	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00875	mg																										
Substance	3	Copper	Supplier	7440-50-8	96.9185	2.0	84.80369	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.175	mg																										

Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.004375	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	2.0	0.00875	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	1.75	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.175	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.35	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.004375	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.04375	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.175	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.375E-4	mg	
Sub-Item	1	Adhesive and Sealants				1.0	100.30061282	mg	
Material	2	Epoxy resin				1.0	100.30061282	mg	
Substance	3	Oxirane, 2,2-[[[(oxiranylmethoxy)phenyl]methylene]bis[(1,1-dimethylethyl)methylphenylene]oxymethylene]]bis-	Supplier	129915-35-1	100.0	1.0	100.30061	mg	N/A
Sub-Item	1	2000 05 0102, COUPLING NUT				2.0	1374.0	mg	
Material	2	Stainless Steel				2.0	1374.0	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	2.0	2.061	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	2.0	13.74	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	2.0	261.06	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	2.0	27.48	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.4	2.0	5.496	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.01374	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.2	2.0	2.748	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.1374	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.1374	mg	
Substance	3	Iron	Supplier	7439-89-6	66.7685	2.0	917.39919	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.35	2.0	4.809	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.1374	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.00687	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	2.0	137.4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	1.374	mg	
Sub-Item	1	2024 09 0163, MALE CONTACT				1.0	200.637	mg	
Material	2	Brass				1.0	195.14	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0019514	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.019514	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.19514	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.019514	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.039028	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0019514	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	0.68299	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	63.90347	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	122.9382	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.757E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.019514	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	7.22018	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.09757	mg	
Material	2	Copper Plate				1.0	0.895	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.95E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	0.8941	mg	
Material	2	Nickel Plate				1.0	1.684	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.003368	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001684	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.67895	mg	
Material	2	Gold Plate				1.0	0.778	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.002334	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.77567	mg	
Material	2	Gold Plate				1.0	2.14	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	2.13358	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.00642	mg	
Sub-Item	1	2024 02 0102, PLUG HSG				1.0	1141.139	mg	
Material	2	Stainless Steel				1.0	1141.139	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	1.71171	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	1.0	11.41139	mg	
Substance	3	Chromium	Supplier	7440-47-3	19.0	1.0	216.81641	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	22.82278	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.4	1.0	4.56456	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01141139	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.2	1.0	2.28228	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.11411	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.11411	mg	
Substance	3	Iron	Supplier	7439-89-6	66.7685	1.0	761.92139	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.35	1.0	3.99399	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.11411	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0057057	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.0	1.0	114.1139	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.14114	mg	