



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-02-21	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-1775801-6	<b>Amount</b>	5446.2322	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	PCI EXPRESS 98P(3.1)(30")BL ACK	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0616</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	Contact				1.0	1303.4	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	1.3034	mg	
Substance	2	Tin	Supplier	7440-31-5	6.75	1.0	87.9795	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	2.6068	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.35	1.0	4.5619	mg	
Substance	2	Copper	Supplier	7440-50-8	92.55	1.0	1206.2967	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.6517	mg	
Material	1	Contact_Tin plating				1.0	6.566	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9	1.0	6.55943	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.006566	mg	
Material	1	Housing				1.0	3980.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	79.6	mg	
Substance	2	Benzene, ethenyl-, ar-bromo derivs., homopolymers	Supplier	148993-99-1	18.0	1.0	716.4	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	1592.0	mg	
Substance	2	Hexanedioic acid, polymer with 1,4-butanediamine	Supplier	50327-77-0	40.0	1.0	1592.0	mg	
Material	1	Board lock				1.0	141.6	mg	
Substance	2	Copper	Supplier	7440-50-8	65.73	1.0	93.07368	mg	
Substance	2	Zinc	Supplier	7440-66-6	34.25	1.0	48.498	mg	
Substance	2	Iron	Supplier	7439-89-6	0.015	1.0	0.02124	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	0.00708	mg	
Material	1	Contact_Au plating				1.0	2.058	mg	

Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.002058	mg	
Substance	2	Gold	Supplier	7440-57-5	99.9	1.0	2.05594	mg	
Material	1	Board lock_Tin plating				1.0	0.6962	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	6.962E-4	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9	1.0	0.6955	mg	
Material	1	Contact_Ni plating				1.0	11.564	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.9	1.0	11.55244	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.011564	mg	
Material	1	Board lock_Ni plating				1.0	0.348	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.9	1.0	0.34765	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	3.48E-4	mg	