



|   |   |  |                           |                      |                                |                      |   |                      |                  |
|---|---|--|---------------------------|----------------------|--------------------------------|----------------------|---|----------------------|------------------|
| <b>Form Type</b>  | Distribute  | <b>Version</b>                             | 2.0                       | <b>Ref</b>           | IPC 1752A                      | <b>Sectionals</b>    | Material Info   | <b>Subsectionals</b> | D, A             |
| <b>Supplier Information</b>   |   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Company Name</b>   | TE Connectivity   | <b>Request Document ID</b>                 |                           | <b>Contact Name</b>  | Benfer, David W                | <b>Contact Title</b> | Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD |                      |                  |
| <b>Company Unique ID</b>  | TE Connectivity   | <b>Response Date</b>                       | 2017-01-20                | <b>Contact Email</b> | dave.benfer@te.com             |                      |   |                      |                  |
| <b>Contact Phone Number</b>   | +1-717-986-3725   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Legal Statement</b>  |   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Supplier Acceptance</b>  | true  |  |                           |                      |                                |                      |   |                      |                  |
| <b>Legal Statement</b>  |   |  |                           |                      |                                |                      |   |                      |                  |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. |   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Product</b>  |   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Manufacturer Item number</b>   | 5-5530843-3   | <b>Amount</b>                              | 8297.470484               | <b>Version</b>       | -                              | <b>Identity</b>      |   |                      |                  |
| <b>Manufacturer Item Name</b>   | CONN SEC II 17 POS 100C/L   | <b>Weight Uom</b>                          | mg                        | <b>Mfr Site</b>      |                                | <b>Authority</b>     |   |                      |                  |
| <b>Date</b>   |   | <b>UOM</b>                                 | Each                      |                      |                                |                      |   |                      |                  |
| <b>EUroHS-0508</b>  | Product(s) meets EU RoHS requirement without any exemptions   |  |                           |                      |                                |                      |   |                      |                  |
| <b>ChinaRoHS-0508</b>   | Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products |  |                           |                      |                                |                      |   |                      |                  |
| <b>EUREACH-1215</b>   | REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH                           |  |                           |                      |                                |                      |   |                      |                  |
| <b>Product Disclosure</b>   |   |  |                           |                      |                                |                      |   |                      |                  |
| <b>Sub-Item/Material/Substance</b>  | <b>Level</b>  | <b>Name</b>                                | <b>Substance Category</b> | <b>Substance CAS</b> | <b>Substance Concentration</b> | <b>Quantity</b>      | <b>Mass per Unit</b>                                  | <b>UOM</b>           | <b>Exemption</b> |
| Sub-Item  | 1   | CONTACT, STD EDGE II, .100 CL              |                           |                      |                                | 34.0                 | 73.484426   | mg                   |                  |
| Material  | 2   | Phos Bronze                                |                           |                      |                                | 34.0                 | 72.5  | mg                   |                  |
| Substance   | 3   | Copper                                     | Supplier                  | 7440-50-8            | 94.6985                        | 34.0                 | 68.65641  | mg                   |                  |
| Substance   | 3   | Manganese                                  | Supplier                  | 7439-96-5            | 0.02                           | 34.0                 | 0.0145  | mg                   |                  |
| Substance   | 3   | Chromium                                   | Supplier                  | 7440-47-3            | 0.01                           | 34.0                 | 0.00725   | mg                   |                  |
| Substance   | 3   | Tin  | Supplier                  | 7440-31-5            | 4.5                            | 34.0                 | 3.2625  | mg                   |                  |
| Substance   | 3   | Arsenic                                    | Supplier                  | 7440-38-2            | 0.0050                         | 34.0                 | 0.003625  | mg                   |                  |
| Substance   | 3   | Iron                                       | Supplier                  | 7439-89-6            | 0.1                            | 34.0                 | 0.0725  | mg                   |                  |
| Substance   | 3   | Antimony                                   | Supplier                  | 7440-36-0            | 0.01                           | 34.0                 | 0.00725   | mg                   |                  |
| Substance   | 3   | Beryllium                                  | Supplier                  | 7440-41-7            | 0.0010                         | 34.0                 | 7.25E-4   | mg                   |                  |
| Substance   | 3   | Zinc                                       | Supplier                  | 7440-66-6            | 0.3                            | 34.0                 | 0.2175  | mg                   |                  |
| Substance   | 3   | Phosphorus                                 | Supplier                  | 7723-14-0            | 0.1                            | 34.0                 | 0.0725  | mg                   |                  |
| Substance   | 3   | Cobalt                                     | Supplier                  | 7440-48-4            | 0.1                            | 34.0                 | 0.0725  | mg                   |                  |
| Substance   | 3   | Cadmium                                    | Cadmium/Cadmium Compounds | 7440-43-9            | 0.0050                         | 34.0                 | 0.003625  | mg                   |                  |
| Substance   | 3   | Lead                                       | Lead/Lead Compounds       | 7439-92-1            | 0.05                           | 34.0                 | 0.03625   | mg                   |                  |
| Substance   | 3   | Nickel                                     | Nickel                    | 7440-02-0            | 0.1                            | 34.0                 | 0.0725  | mg                   |                  |
| Substance   | 3   | Mercury                                    | Mercury/Mercury Compounds | 7439-97-6            | 5.0E-4                         | 34.0                 | 3.625E-4  | mg                   |                  |
| Material  | 2   | Nickel Plate                               |                           |                      |                                | 34.0                 | 0.7519  | mg                   |                  |
| Substance   | 3   | Lead                                       | Lead/Lead Compounds       | 7439-92-1            | 0.1                            | 34.0                 | 7.519E-4  | mg                   |                  |
| Substance   | 3   | Contains No Reportable TE5081-2 Substances | Supplier                  | TE5081-2-1212        | 0.2                            | 34.0                 | 0.0015038   | mg                   |                  |
| Substance   | 3   | Nickel                                     | Nickel                    | 7440-02-0            | 99.7                           | 34.0                 | 0.74964   | mg                   |                  |
| Material  | 2   | Gold Plate                                 |                           |                      |                                | 34.0                 | 0.0172  | mg                   |                  |
| Substance   | 3   | Gold                                       | Supplier                  | 7440-57-5            | 99.7                           | 34.0                 | 0.0171484   | mg                   |                  |
| Substance   | 3   | Contains No Reportable TE5081-2 Substances | Supplier                  | TE5081-2-1212        | 0.3                            | 34.0                 | 5.16E-5   | mg                   |                  |
| Material  | 2   | Tin Plate                                  |                           |                      |                                | 34.0                 | 0.215326  | mg                   |                  |
| Substance   | 3   | Contains No Reportable TE5081-2 Substances | Supplier                  | TE5081-2-1212        | 0.2                            | 34.0                 | 4.3065E-4   | mg                   |                  |

|           |   |  |                     |               |       |      |           |    |  |
|-----------|---|--|---------------------|---------------|-------|------|-----------|----|--|
| Substance | 3 | Tin  | Supplier            | 7440-31-5     | 99.73 | 34.0 | 0.21474   | mg |  |
| Substance | 3 | Lead   | Lead/Lead Compounds | 7439-92-1     | 0.07  | 34.0 | 1.5073E-4 | mg |  |
| Sub-Item  | 1 | STD EDGE II HSG 17 POS 100C/L  |                     |               |       | 1.0  | 5799.0    | mg |  |
| Material  | 2 | PBT-I-GF30-FR(17)  |                     |               |       | 1.0  | 5799.0    | mg |  |
| Substance | 3 | Dolomite (CaMg(CO3)2)  | Supplier            | 16389-88-1    | 0.5   | 1.0  | 28.995    | mg |  |
| Substance | 3 | Glass, oxide, chemicals  | Supplier            | 65997-17-3    | 35.0  | 1.0  | 2029.65   | mg |  |
| Substance | 3 | Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester | Supplier            | 6683-19-8     | 0.2   | 1.0  | 11.598    | mg |  |
| Substance | 3 | Furan, tetrahydro-   | Supplier            | 109-99-9      | 0.2   | 1.0  | 11.598    | mg |  |
| Substance | 3 | Contains No Reportable TE5081-2 Substances   | Supplier            | TE5081-2-1212 | 3.0   | 1.0  | 173.97    | mg |  |
| Substance | 3 | Talc (Mg3H2(SiO3)4)  | Supplier            | 14807-96-6    | 2.0   | 1.0  | 115.98    | mg |  |
| Substance | 3 | Ethene, 1,1,2,2-tetrafluoro-, homopolymer  | Supplier            | 9002-84-0     | 1.0   | 1.0  | 57.99     | mg |  |
| Substance | 3 | Chlorite-group minerals  | Supplier            | 1318-59-8     | 0.5   | 1.0  | 28.995    | mg |  |
| Substance | 3 | Carbon black   | Supplier            | 1333-86-4     | 1.0   | 1.0  | 57.99     | mg |  |
| Substance | 3 | 1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol  | Supplier            | 30965-26-5    | 36.6  | 1.0  | 2122.434  | mg |  |
| Substance | 3 | Phosphoric acid, zinc salt (2:3)   | Supplier            | 7779-90-0     | 0.5   | 1.0  | 28.995    | mg |  |
| Substance | 3 | Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)  | Supplier            | 1043-4-FR17   | 18.0  | 1.0  | 1043.82   | mg |  |
| Substance | 3 | Quartz (SiO2)  | Supplier            | 14808-60-7    | 0.5   | 1.0  | 28.995    | mg |  |
| Substance | 3 | 2-Propenenitrile, polymer with ethenylbenzene  | Supplier            | 9003-54-7     | 1.0   | 1.0  | 57.99     | mg |  |