



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-09-30	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5104338-2	Amount	1677.456908	Version	-	Identity			
Manufacturer Item Name	A/L LOW PRO HDR 14P VERT HT	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	BAND ASSY .0245 SQ POST .493 15 PD-NI				14.0	15.951922	mg	
Material	2	Tin Plate				14.0	0.0246	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	14.0	4.92E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	14.0	0.02453358	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	14.0	1.722E-5	mg	
Material	2	Brass Wire				14.0	15.19	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	14.0	10.86085	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	14.0	1.519E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	14.0	4.25663	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	14.0	0.007595	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	14.0	1.519E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	14.0	0.007595	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	14.0	0.01519	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	14.0	0.00150381	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	14.0	0.001519	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	14.0	0.007595	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	14.0	7.595E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	14.0	7.595E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	14.0	0.03038	mg	
Material	2	Gold Plate				14.0	0.02361	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.02353917	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	14.0	7.083E-5	mg	
Material	2	Palladium-Nickel Plate				14.0	0.184642	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	14.0	0.14771	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	14.0	0.0369284	mg	
Material	2	Nickel Plate				14.0	0.52907	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	14.0	0.00105814	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	14.0	5.2907E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	14.0	0.52748	mg	
Sub-Item	1	014 HOUSING LOPRO HDR HT				1.0	1454.13	mg	
Material	2	PPA-GF33				1.0	1454.13	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	23.3	1.0	338.81229	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	21.81195	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.2	1.0	511.85376	mg	
Substance	3	Antimonate (SbO3 ¹⁻), sodium (1:1)	Supplier	15432-85-6	3.9	1.0	56.71107	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.3	1.0	4.36239	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	34.5	1.0	501.67485	mg	
Substance	3	Calcium oxide (CaO)	Supplier	1305-78-8	0.4	1.0	5.81652	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	13.08717	mg	