



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-04-07	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-5175472-6	<b>Amount</b>	6045.0	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	CHAMP 050 B/B PLUG H W/LEG 50P	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0616</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	CHAMP 050 PLUG HSG 50P H				1.0	3660.0	mg	
Material	2	PA66-GF20FR				1.0	3660.0	mg	
Substance	3	2,5-Furandione, polymers with hydrogenated butadiene-styrene polymer, block, graft	Supplier	113569-15-6	2.0	1.0	73.2	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.-hydroxy-	Supplier	25322-68-3	0.1	1.0	3.66	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	10.0	1.0	366.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	732.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	25.0	1.0	915.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	54.9	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]]	Supplier	32131-17-2	36.9	1.0	1350.54	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	109.8	mg	
Substance	3	Benzenepropamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.5	1.0	18.3	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	36.6	mg	

Sub-Item	1	RETENTION LEG				2.0	95.0	mg	
Material	2	Tin Plate				2.0	0.5925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001185	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	0.5909	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	4.1475E-4	mg	
Material	2	Brass				2.0	93.4745	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	9.3474E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	26.19389	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.04673725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00934745	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.04673725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.0934745	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	66.83427	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	9.3474E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.00934745	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.6737E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.18695	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00467373	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.04673725	mg	
Material	2	Nickel Plate				2.0	0.933	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001866	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	9.33E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.9302	mg	
Sub-Item	1	CHAMP 050 TINE PLATE 50P				1.0	710.0	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	710.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	3.55	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	248.5	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	1.42	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	1.42	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	21.3	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	14.2	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	7.1	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	3.55	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	7.1	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	259.86	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	3.55	mg	

Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	127.8	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	3.55	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	7.1	mg	
Sub-Item	1	CHAMP 050 I BTB PLUG H CONT				25.0	33.8	mg	
Material	2	Phos Bronze				25.0	32.41842	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	25.0	30.69976	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	25.0	0.00648368	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.00324184	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	25.0	1.45883	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	25.0	0.00162092	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	25.0	0.03241842	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.00324184	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	3.2418E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	25.0	0.09725526	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	25.0	0.03241842	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.03241842	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	25.0	0.00162092	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.01620921	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	25.0	0.03241842	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	1.6209E-4	mg	
Material	2	Tin Plate				25.0	0.8335	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	0.001667	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	25.0	0.83125	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	25.0	5.8345E-4	mg	
Material	2	Gold Plate				25.0	0.06272	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.06253184	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	25.0	1.8816E-4	mg	
Material	2	Nickel Plate				25.0	0.48536	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	9.7072E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	4.8536E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	0.4839	mg	
Sub-Item	1	CHAMP 050 B-T-B PLUG CONT H AU				25.0	25.6	mg	
Material	2	Phos Bronze				25.0	24.60564	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	25.0	23.30117	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	25.0	0.00492113	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	25.0	0.00246056	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	25.0	1.10725	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	25.0	0.00123028	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	25.0	0.02460564	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	0.00246056	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	2.4606E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	25.0	0.07381692	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	25.0	0.02460564	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	0.02460564	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	25.0	0.00123028	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	0.01230282	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	25.0	0.02460564	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	1.2303E-4	mg	
Material	2	Tin Plate				25.0	0.55566	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	0.00111132	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	25.0	0.55416	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	25.0	3.8896E-4	mg	
Material	2	Gold Plate				25.0	0.06272	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	0.06253184	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	25.0	1.8816E-4	mg	
Material	2	Nickel Plate				25.0	0.37598	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	7.5196E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	3.7598E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	0.37485	mg	