



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-08-07	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5499910-2	<b>Amount</b>	4657.8749284	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	A/L UNIV HDR 14P VERT SHT LAT	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				14.0	51.6767806	mg	
Material	2	Nickel Plate				14.0	0.947992	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	14.0	0.00189598	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	14.0	9.4799E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	14.0	0.94515	mg	
Material	2	Tin Plate				14.0	0.197382	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	14.0	1.9718E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	14.0	0.19718	mg	
Material	2	Brass				14.0	50.46	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	14.0	0.05046	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	14.0	32.2944	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	14.0	0.02523	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	14.0	5.046E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	14.0	0.005046	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	14.0	0.05046	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	14.0	0.05046	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	14.0	17.76621	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	14.0	0.005046	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	14.0	0.005046	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	14.0	0.02523	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	14.0	0.15138	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.01	14.0	0.005046	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	14.0	2.523E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	14.0	0.02523	mg	
Material	2	Gold Plate				14.0	0.0283906	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.3	14.0	8.51718E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.02830543	mg	
Material	2	Gold Plate				14.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.04288695	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	14.0	1.2905E-4	mg	
Sub-Item	1	UNV AMP-LATCH HDR HSG 14P W/MT				1.0	3140.0	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	3140.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	15.7	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	1099.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	6.28	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	6.28	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	94.2	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	62.8	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	31.4	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	15.7	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	31.4	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	1149.24	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	15.7	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	565.2	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	15.7	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	31.4	mg	
Sub-Item	1	UNIVERSAL HEADER LATCH				2.0	397.2	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	397.2	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	1.986	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	139.02	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.7944	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.7944	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	11.916	mg	

Substance	3	Talc (Mg <sub>3</sub> H <sub>2</sub> (SiO <sub>3</sub> ) <sub>4</sub> )	Supplier	14807-96-6	2.0	2.0	7.944	mg	
Substance	3	Ethene, 1,1,2,2- tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	3.972	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	1.986	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	3.972	mg	
Substance	3	1,4- Benzenedicarb oxylic acid, 1,4- dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	145.3752	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	1.986	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	71.496	mg	
Substance	3	Quartz (SiO <sub>2</sub> )	Supplier	14808-60-7	0.5	2.0	1.986	mg	
Substance	3	2- Propenenitrile, polymer with ethenylbenzen e	Supplier	9003-54-7	1.0	2.0	3.972	mg	