



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-04-20	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1717831-1	Amount	1136.5	Version	-	Identity			
Manufacturer Item Name	MINI PCI EXPRESS SEMI HARD TRAY CONN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MINI PCI EXPRESS CONN 52P ASSY				1.0	1136.5	mg	
Material	2	Nickel Plate				1.0	26.52	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.05304	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02652	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	26.44044	mg	
Material	2	Gold Plate				1.0	0.676	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.67397	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.002028	mg	
Material	2	Nickel Plate				1.0	0.2	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.0E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	4.0E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.1994	mg	
Material	2	Phos Bronze				1.0	336.804	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.3368	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0336804	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.67361	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0168402	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	303.28695	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0673608	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.17881	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00336804	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.3368	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.0336804	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	30.31236	mg	

Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.3368	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00168402	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0168402	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1684	mg	
Material	2	Phos Bronze				1.0	18.8	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	17.80332	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.00376	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.00188	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.846	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	9.4E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.0188	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00188	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.88E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.0564	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.0188	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0188	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	9.4E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0094	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.0188	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.4E-5	mg	
Material	2	LCP-GF30				1.0	752.5	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	1.505	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	22.575	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	15.05	mg	
Substance	3	2,6-Naphthalenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoic acid	Supplier	126710-21-2	65.8	1.0	495.145	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	218.225	mg	
Material	2	Tin Plate				1.0	1.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0020	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.9973	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	7.0E-4	mg	