



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Sectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Chan, Nelson	Contact Title	Manager Sales, HKG SELL DIR-EMS		
Company Unique ID	TE Connectivity	Response Date	2015-12-12	Contact Email	nelson.chan@te.com				
Contact Phone Number	+852-2738-8751								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5767096-8	Amount	1386.45365822	Version	-	Identity			
Manufacturer Item Name	MICT,REC,038,ASY,.025,TAPE,CAP	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	20.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	38 POS. MICTOR RECEPTACLE HOUS				1.0	916.0	mg	
Material	2	LCP-GF30				1.0	916.0	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	1.832	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	27.48	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	18.32	mg	
Substance	3	2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarb oxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoi c acid	Supplier	126710-21-2	65.8	1.0	602.728	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	265.64	mg	
Sub-Item	1	VACUUM P/U CAP,REC LOOSE PIECE				1.0	111.4	mg	
Material	2	Aluminum Alloy				1.0	111.4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.1114	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.05	1.0	0.0557	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.35	1.0	0.3899	mg	

Substance	3	Antimony	Supplier	7440-36-0	0.05	1.0	0.0557	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	1.0	0.4456	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.25	1.0	0.2785	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.05	1.0	0.0557	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.05	1.0	0.0557	mg	
Substance	3	Aluminum	Supplier	7429-90-5	95.5945	1.0	106.49227	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	1.0	0.1114	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.1	1.0	0.1114	mg	
Substance	3	Magnesium	Supplier	7439-95-4	2.8	1.0	3.1192	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.0557	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	5.57E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0557	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00557	mg	
Sub-Item	1	LF MICTOR RECEPTACLE SIGNAL CO				38.0	7.90689454	mg	
Material	2	Copper Alloy				38.0	7.66	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	38.0	0.00383	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	38.0	0.0766	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	38.0	0.09192	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	38.0	0.00766	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7685	38.0	7.10607	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	38.0	0.004596	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	38.0	7.66E-5	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	38.0	0.02298	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	38.0	0.00766	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	38.0	0.01532	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	38.0	3.83E-4	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	38.0	7.66E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	38.0	0.32172	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	38.0	3.83E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	38.0	3.83E-5	mg	
Material	2	Gold Plate				38.0	0.00743317	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	38.0	0.00741087	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	38.0	2.229951E-5	mg	
Material	2	Tin Plate				38.0	0.00946137	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	38.0	1.0E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	38.0	0.00945192	mg	
Material	2	Nickel Plate				38.0	0.23	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	38.0	4.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	38.0	2.3E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	38.0	0.22931	mg	
Sub-Item	1	MICTOR RECEPTACLE GROUND BUS CONTACT				1.0	58.5916657	mg	
Material	2	Gold Plate				1.0	0.0514821	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.05132765	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	1.5445E-4	mg	
Material	2	Tin Plate				1.0	0.0601836	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	6.012342E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	1.0	0.06012348	mg	
Material	2	Nickel Plate				1.0	1.9	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0038	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0019	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.8943	mg	

Material	2	Phos Bronze				1.0	56.58	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	53.58041	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.011316	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.005658	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	2.5461	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.002829	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.05658	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.005658	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.658E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.16974	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.05658	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.05658	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.002829	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.02829	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.05658	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.829E-4	mg	