



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals		Material Info		Subsectionals	D, A
<b>Supplier Information</b>											
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Engineer Product Compliance china				
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-09-19	<b>Contact Email</b>	cc.wu@te.com						
<b>Contact Phone Number</b>	86-2124071672										
<b>Legal Statement</b>											
<b>Supplier Acceptance</b>	true										
<b>Legal Statement</b>											
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.											
<b>Product</b>											
<b>Manufacturer Item number</b>	4-643814-5	<b>Amount</b>	2811.25	<b>Version</b>	-	<b>Identity</b>					
<b>Manufacturer Item Name</b>	15P MTA100 CONN ASSY POL RIB	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>					
<b>Date</b>		<b>UOM</b>	Each								
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions										
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products										
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH										
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed										
<b>Product Disclosure</b>											
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption		
Sub-Item	1	15P MTA100 HSG 24AWG WHITE				1.0	1428.7	mg			
Material	2	PA66				1.0	1400.126	mg			
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	99.355	1.0	1391.09519	mg			
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.02800252	mg			
Substance	3	Octadecanamide, N,N-1,2-ethanediybis-	Supplier	110-30-5	0.3	1.0	4.20038	mg			
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	2.80025	mg			
Substance	3	Aluminum, hydroxybis(octadecanoato-kappa.O)-	Supplier	300-92-5	0.14	1.0	1.96018	mg			
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	0.04200378	mg			
Material	2	COLORANT				1.0	28.574	mg			
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	14.76	1.0	4.21752	mg			
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	1.0	1.0	0.28574	mg			
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	84.24	1.0	24.07074	mg			
Sub-Item	1	MTA100 CONT 24AWG SN / PHBZ				15.0	92.17	mg			
Material	2	Tin Plate				15.0	1.72	mg			
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	15.0	0.00344	mg			
Substance	3	Tin	Supplier	7440-31-5	99.73	15.0	1.71536	mg			
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	15.0	0.001204	mg			
Material	2	Phos Bronze				15.0	90.0	mg			

Substance	3	Manganese	Supplier	7439-96-5	0.02	15.0	0.018	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1485	15.0	83.83365	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	15.0	0.27	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	15.0	0.0090	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	15.0	0.315	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	15.0	0.09	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	15.0	0.0045	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	15.0	9.0E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	15.0	0.09	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	15.0	0.0090	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	15.0	5.22	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	15.0	0.0045	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	15.0	4.5E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	15.0	0.045	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	15.0	0.09	mg	
Material	2	Nickel Plate				15.0	0.45	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	15.0	9.0E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	15.0	4.5E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	15.0	0.44865	mg	