



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-02-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5787834-1	Amount	3762.067428	Version	-	Identity			
Manufacturer Item Name	USB 4P VERTICAL TYPE B RECEPTACLE CONN.	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	PLATED SHELL, LOOSE PIECE				1.0	2215.7474	mg	
Material	2	Nickel Plate				1.0	27.1912	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0543824	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0271912	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	27.10963	mg	
Material	2	Phos Bronze				1.0	2149.57	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	2035.61055	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.42991	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.21496	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	96.73065	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.10748	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	2.14957	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.21496	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0214957	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	6.44871	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	2.14957	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.14957	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.10748	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.07478	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	2.14957	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01074785	mg	
Material	2	Tin Plate				1.0	38.9862	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.02729034	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0779724	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	38.88094	mg	

Sub-Item	1	CONTACT USB VERTICAL RECEPTACLE LEAD FREE				4.0	10.770007	mg	
Material	2	Nickel Plate				4.0	0.873042	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.00174608	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	8.7304E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.87042	mg	
Material	2	Phos Bronze				4.0	9.5429095	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	4.0	9.03699	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.00190858	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	9.5429E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	0.42943	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	4.0	4.7715E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.00954291	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	9.5429E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	9.54291E-5	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.02862873	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	0.00954291	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.00954291	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	4.7715E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.00477145	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.00954291	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	4.771455E-5	mg	
Material	2	Gold Plate				4.0	0.0037275	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	4.0	0.00371632	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	4.0	1.11825E-5	mg	
Material	2	Palladium-Nickel Plate				4.0	0.08463	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	4.0	0.067704	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	4.0	0.016926	mg	
Material	2	Tin Plate				4.0	0.265698	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	5.314E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	0.26498	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	1.8599E-4	mg	
Sub-Item	1	USB B VRT RCPT HSG BLK				1.0	1503.24	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	1503.24	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	7.5162	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	526.134	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	3.00648	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	3.00648	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	45.0972	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	30.0648	mg	

Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	15.0324	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	7.5162	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	15.0324	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	550.18584	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	7.5162	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	270.5832	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	7.5162	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	15.0324	mg	