



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Prod Compliance Engineer, China CIS Compliance		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-31	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	640445-7	<b>Amount</b>	2524.507	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	07P MTA156 HDR ASSY FL/STR SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Brass Square				1.0	1257.707	mg	
Material	2	Nickel Plate				1.0	5.69903236	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01139806	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00569903	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	5.68194	mg	
Material	2	Brass Wire				1.0	1242.66956676	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	888.50874	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0124267	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	348.22832	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.62133	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0124267	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.62133	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.24267	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.12302	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.12427	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.62133	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.06213348	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00621335	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	2.48534	mg	
Material	2	Tin Plate				1.0	9.33840088	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0186768	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	9.31319	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00653688	mg	
Sub-Item	1	Polyester Compound				1.0	1266.8	mg	
Material	2	PBT-GF7				1.0	1266.8	mg	

Substance	3	4,4'-isopropylidene diphenol (bisphenol A; BPA)	Supplier	80-05-7	0.01	1.0	0.12668	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	82.342	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	380.04	mg	
Substance	3	Antimony oxide (Sb <sub>2</sub> O <sub>3</sub> )	Supplier	1309-64-4	8.0	1.0	101.344	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	12.668	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	690.27932	mg	