



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Prod Compliance Engineer, China CIS Compliance		
Company Unique ID	TE Connectivity	Response Date	2017-01-27	Contact Email	cc.wu@te.com				
Contact Phone Number	+86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640456-2	Amount	209.924	Version	-	Identity			
Manufacturer Item Name	02P MTA100 HDR ASSY F/L SQ STR	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Compound				1.0	120.0	mg	
Material	2	PBT				1.0	120.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.24	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	6.0	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.12	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	9.6	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	0.12	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	0.6	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	0.12	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	0.6	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	36.0	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	6.0	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	2.4	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	0.12	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	58.08	mg	
Sub-Item	1	Brass Square				1.0	89.924	mg	
Material	2	Brass Wire				1.0	89.02476	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	63.6527	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	8.9025E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	24.94705	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.04451238	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	8.9025E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.04451238	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.08902476	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.00881345	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00890248	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.04451238	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00445124	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.4512E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.17805	mg	
Material	2	Nickel Plate				1.0	0.404658	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	8.0932E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.0466E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.40344	mg	
Material	2	Tin Plate				1.0	0.494582	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	9.8916E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.49325	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	3.4621E-4	mg	