



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-10-14	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	640586-1	<b>Amount</b>	5520.0	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	08P UMNL PLUG HSG V2 NATL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Nylon Compound				1.0	5520.0	mg	
Material	2	PA66				1.0	5520.0	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	99.355	1.0	5484.396	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.1104	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediy]bis-	Supplier	110-30-5	0.3	1.0	16.56	mg	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	11.04	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-.kappa.O)-	Supplier	300-92-5	0.14	1.0	7.728	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	0.1656	mg	