



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Prod Compliance Engineer, China CIS Compliance		
Company Unique ID	TE Connectivity	Response Date	2017-01-27	Contact Email	cc.wu@te.com				
Contact Phone Number	+86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	641937-1	Amount	812.69627	Version	-	Identity			
Manufacturer Item Name	03P MTA156 HDR ASSY STR W/O#2	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Compound				1.0	431.5	mg	
Material	2	PBT-GF7				1.0	431.5	mg	
Substance	3	4,4'-isopropylidene diphenol (bisphenol A; BPA)	Supplier	80-05-7	0.01	1.0	0.04315	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	28.0475	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	129.45	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	34.52	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	4.315	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	235.12435	mg	
Sub-Item	1	Brass Square				1.0	381.19627	mg	
Material	2	Brass Wire				1.0	376.6386	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	269.2966	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00376639	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	105.54393	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.18832	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00376639	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.18832	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.37664	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.03728722	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03766386	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.18832	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01883193	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00188319	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.75328	mg	
Material	2	Nickel Plate				1.0	1.72731	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00345462	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00172731	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.72213	mg	
Material	2	Tin Plate				1.0	2.83036	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00566072	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	2.82272	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00198125	mg	