

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2017

© COPYRIGHT 2017

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	4	GTIN NRS ADDED, PIN TXT ADDED	11MAR2019	GCM	MG

NOTES:

- MATERIALS:
HOUSING: GLASS FILLED PBT, HALOGEN FREE FLAME RETARDANT
COLOR : NATURAL
CONTACTS: GOLD PLATED COPPER ALLOY
- PRODUCT COMPLIES WITH RESTRICTION ON HAZARDOUS SUBSTANCES
DIRECTIVE 2011/65/EU
- SCREW TO BE USED - PAN HEAD M3, #4-40, LENGTH 12mm MIN.
RECOMMENDED SCREW TORQUE: 0.4 - 0.6 Nm
- LED RETENTION ON 2 CORNERS WITH DOUBLE SIDED ADHESIVE TAPE.
- MATING CONNECTOR TE PART NO: 353908-4 OR 2-353908-4 OR 6-353908-4
- DIMENSIONS SHOWN ARE IN MATED POSITION WITH LED
- SEE SHEET 3 FOR RECOMMENDED PIN LAYOUT & ADDITIONAL INFORMATION
- ELECTRICAL RATINGS:
- USE WITH A 48V DC CONSTANT VOLTAGE CLASS 2 POWER SUPPLY, ±10% TOLERANCE
- LED FORWARD VOLTAGE HAVE THE FOLLOWING RANGE: 25 - 41VDC.

HOLES FOR M3/4-40 SCREWS

DALI 2 LOGO

REMOVE RELEASE
LINER BEFORE
ASSEMBLING LED

LED CONTACT

Ø 50,0

7,6

7,5 Max

3,0

DETAIL Z

SECTION A-A

DETAIL Z

2316511-1
YYWWD

Ø 3,3
(2x)

MAX OPERATING TEMP : 125°C
TYPICAL OUTPUT VOLTAGE : 36VDC
MAX OUTPUT CURRENT : 350mA

35,0

PRELIMINARY PART
NOT RELEASED FOR PRODUCTION

CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING


Engineer: SUBHASH.M

PRODUCT DATA SHEET 1-1773935-6
FOR ADDITIONAL INFORMATION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL
SEE NOTES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.1
2 PLC ±0.1
3 PLC ±0.1
4 PLC ±0.1
ANGLES ±0.1
FINISH -

DWN 22NOV2017

SUBHASH.M

CHK 22NOV2017

MARCO.Z

APVD 15DEC2017

O.I.FINSE

PRODUCT SPEC

108-133109

APPLICATION SPEC

114-133109

WEIGHT

SEE TABLE

CUSTOMER DRAWING

NAME

LUMAWISE DRIVE TYPE Z50,
DALI VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-2316511

SCALE

2:1

SHEET


1 OF 4

REV


4

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


AS SHOWN 2316511-1
SCALE 1:1








AS SHOWN 2316511-2
SCALE 1:1




AS SHOWN 2316511-3
SCALE 1:1



AS SHOWN 2316511-4
SCALE 1:1



PRELIMINARY PART
NOT RELEASED FOR PRODUCTION
CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING
Engineer: SUBHASH.M

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M 22NOV2017		 TE Connectivity						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK MARCO.Z 22NOV2017		NAME LUMAWISE DRIVE TYPE Z50, DALI VERSION				
		0 PLC ±- 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD O.I.F.I.J.N.S.F. 15DEC2017						
				PRODUCT SPEC 108-133109						
				APPLICATION SPEC 114-133109						
MATERIAL SEE NOTES		FINISH - -		WEIGHT SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-2316511	RESTRICTED TO -	
				CUSTOMER DRAWING				SCALE 2:1	SHEET 2 OF 4	REV 4

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2017


© COPYRIGHT 2017 BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

RECOMMENDED DRILLING HOLE PATTERN




PIN LAYOUT

SCALE 4:1



P1	DALI (+)	DA
P2	DALI (-)	DA
P3	48VIN (+)	U+
P4	48VIN (-) GND	U-


DRILLING LOCATION FOR Tc TESTING
ONLY TOP COVER SHOWN




NOMINAL LED INFO:

THE SKETCH BELOW IS SHOWING THE ZHAGA BOOK 12 COB DIMENSIONS TO MATCH WITH THE LUMAWISE DRIVE TYPE Z50 LED HOLDER


24x24 LAYOUT




20x24 LAYOUT



19x19 LAYOUT



16x19 LAYOUT



**PRELIMINARY PART
NOT RELEASED FOR PRODUCTION**

CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING

Engineer: SUBHASH.M

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±0.2
	2 PLC ±0.1
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
SEE NOTES	-
	-

DWN	SUBHASH.M	22NOV2017
CHK	MARCO.Z	22NOV2017
APVD	O.I.FIUNSE	15DEC2017
PRODUCT SPEC	108-133109	
APPLICATION SPEC	114-133109	
WEIGHT	SEE TABLE	
CUSTOMER DRAWING		



TE Connectivity

LUMAWISE DRIVE TYPE Z50,
DALI VERSION

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2316511	-
SCALE	2:1	SHEET	3 OF 4
REV	4		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

L2C5-xxxx1202E0900; L2C5-xxxx1203E0900 1202s; 120206xCx; 1202CRSP; 1203CRSP	LUMILEDS	16x19
NVCWL024Z; NFCWL060B-V1; NFCLL060B-V1; NFCWL036B-V1M3	NICHIA	
LC040C	SAMSUNG	
BXRH-40E8000-J-23; BXRE-xxxxxxx-x-7x	BRIDGELUX	19x19
PB16H; PB16U; PB19H; PB19U; PB26U;PB26H	LEXTAR	
CLU038-1208C4; CLU721-1206C4; CLU710-1204C1; CLU711-1204C1; CLU034-1205C4; CLU036-1205C1; CLU032-1205A5-303M1A2; CLU720-1206C1; CLL030-1212A1-50KL1A1	CITIZEN	
2PHE20CW27P34001/2PHE30CW27P34001 2PHE20CW38P34001/2PHE30CW38P34002 HM CRI80 Series; HM CRI90 Series SL Series	EDISON OPTO	
EA1919 36V/26W Series	EVERLIGHT	
CHM-11/CXM11; CXM14/CHM14; CLM-14 Gen 3; CXM-11-XH00	LUMINUS	
Soleriq 13 Gen 2 Soleriq 15	OSRAM	
DMS124***G; DMC124/125***F; DMS125/126/128***G; DMC128***F; DMS099***F	PANASONIC	
SDW02F1C; SDWx3F1C	SEOUL	
SLE-G5-LES15 SLE-G5-LES17	TRIDONIC	
LC016/19/26D; LC019D; LC026D	SAMSUNG	
LHC1-3070-1205; L2C5-xxxx-1204 LCHC1-xxxx1204; 1204CRSP; 1205CRSP; 1208CRSP; 1204; 1205; 1208	LUMILEDS	20x24
EAHP2024	EVERLIGHT	
GW6TGBJC50C; GW5DGC**M04	SHARP	
BXRE-xxxxxxx-x-7x	BRIDGELUX	24x24
Soleriq S19 GW KAHLB2.CM	OSRAM	
LED DESCRIPTION	MANUFACTURE NAME	LED TYPE


LEDs COMPATIBILITY

PRELIMINARY PART
NOT RELEASED FOR PRODUCTION

CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING

Engineer: SUBHASH.M

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±- 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±- 4 PLC ±- ANGLES ±-
MATERIAL	FINISH
SEE NOTES	- -

DWN	22NOV2017	TE Connectivity			
CHK	22NOV2017				
APVD	15DEC2017				
Q.I.F.I.J.N.S.F.					
PRODUCT SPEC	108-133109	NAME LUMAWISE DRIVE TYPE Z50, DALI VERSION			
APPLICATION SPEC	114-133109				
WEIGHT	SEE TABLE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING		A3	00779	2316511	-
		SCALE	5:1	SHEET	4 OF 4
				REV	4