



| | | | | | | | | | |
|---|---|---|---------------------------|----------------------|--------------------------------|----------------------|--|----------------------|------------------|
| Form Type | Distribute | Version | 2.0 | Ref | IPC 1752A | Sectionals | Material Info | Subsectionals | D, A |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | Wu, Cc | Contact Title | Prod Compliance Engineer, China CIS Compliance | | |
| Company Unique ID | TE Connectivity | Response Date | 2017-01-31 | Contact Email | cc.wu@te.com | | | | |
| Contact Phone Number | 86-21-33259321 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 770170-1 | Amount | 1235.4 | Version | - | Identity | | | |
| Manufacturer Item Name | 03P MINI-UMNL ASSY VO SNNI* | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EUROHS-0508 | Product(s) does not meet EU RoHS requirements and is not under exemptions | | | | | | | | |
| ChinaRoHS-0508 | Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products | | | | | | | | |
| EUREACH-1215 | REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH | | | | | | | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | 03P MINI-UMNL HDR HSG VO WHT | | | | 1.0 | 900.0 | mg | |
| Material | 2 | PA | | | | 1.0 | 900.0 | mg | |
| Substance | 3 | Water | Supplier | 7732-18-5 | 0.3262 | 1.0 | 2.9358 | mg | |
| Substance | 3 | 2H-Azepin-2-one, hexahydro- | Supplier | 105-60-2 | 0.4637 | 1.0 | 4.1733 | mg | |
| Substance | 3 | Siloxanes and Silicones, di-Me | Supplier | 63148-62-9 | 3.0E-4 | 1.0 | 0.0027 | mg | |
| Substance | 3 | Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy] | Supplier | 32131-17-2 | 0.9451 | 1.0 | 8.5059 | mg | |
| Substance | 3 | Benzenepropanamide, N,N-1,6-hexanediybis[3,5-bis(1,1-dimethylethyl)-4-hydroxy- | Supplier | 23128-74-7 | 0.4004 | 1.0 | 3.6036 | mg | |
| Substance | 3 | 1,2-Ethanediamine | Supplier | 107-15-3 | 0.0033 | 1.0 | 0.0297 | mg | |
| Substance | 3 | Phosphoric acid, sodium salt, hydrate (1:2:12) | Supplier | 10039-32-4 | 0.025 | 1.0 | 0.225 | mg | |
| Substance | 3 | Octadecanoic acid, calcium salt (2:1) | Supplier | 1592-23-0 | 0.2012 | 1.0 | 1.8108 | mg | |
| Substance | 3 | Octadecanamide, N,N-1,2-ethanediybis- | Supplier | 110-30-5 | 0.1901 | 1.0 | 1.7109 | mg | |
| Substance | 3 | 1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1) | Supplier | 37640-57-6 | 9.0717 | 1.0 | 81.6453 | mg | |
| Substance | 3 | Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine | Supplier | 24993-04-2 | 88.373 | 1.0 | 795.357 | mg | |

| | | | | | | | | | |
|-----------|---|---|----------------------------------|-------------------|---------|-----|----------|----|--|
| Sub-Item | 1 | MINI UMNL BAND PIN SNNI* | | | | 3.0 | 111.8 | mg | |
| Material | 2 | Nickel Plate | | | | 3.0 | 0.6 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2- 1212 | 0.2 | 3.0 | 0.0012 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 3.0 | 6.0E-4 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 3.0 | 0.5982 | mg | |
| Material | 2 | Tin-Lead Plate | | | | 3.0 | 0.2 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 86.5 | 3.0 | 0.173 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2- 1212 | 0.5 | 3.0 | 0.0010 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 13.0 | 3.0 | 0.026 | mg | |
| Material | 2 | Brass Wire | | | | 3.0 | 111.0 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 71.5 | 3.0 | 79.365 | mg | |
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.0010 | 3.0 | 0.00111 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 28.0226 | 3.0 | 31.10509 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 0.05 | 3.0 | 0.0555 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 0.0010 | 3.0 | 0.00111 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.05 | 3.0 | 0.0555 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.1 | 3.0 | 0.111 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.0099 | 3.0 | 0.010989 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 3.0 | 0.0111 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.05 | 3.0 | 0.0555 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cad mium Compounds | 7440-43-9 | 0.0050 | 3.0 | 0.00555 | mg | |
| Substance | 3 | Mercury | Mercury/Mercu ry Compounds | 7439-97-6 | 5.0E-4 | 3.0 | 5.55E-4 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 0.2 | 3.0 | 0.222 | mg | |