

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50	F	REVISED PER ECR-19-003798	14JUN2019	BDA DS

SUGGESTED MATING TAB

SHOULDER MAY BE ELIMINATED IF NOT FEASIBLE

1 DFE SYMBOL PER TABLE
 2 PREPRODUCTION - FASR REQUIRED
 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3D VIEW

1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
 2 - NO BURRS PERMISSIBLE AT HOLE.
 3 - MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.
 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076[.003]
 * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	7/3/96		TE Connectivity																		
DIMENSIONS: mm [INCHES]		CHK	M FEHER	7/3/96		NAME																		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J GILLESPIE	7/3/96		HOUSING, RECPT, POSITIVE-LOCK, MKIII, 2 CIRCUIT, 6.35 [.250] SERIES																		
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>0.25 [.010]</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-		1 PLC	±	-	2 PLC	±	-	3 PLC	±	0.25 [.010]	4 PLC	±	-	ANGLES	±	-	PRODUCT SPEC		RESTRICTED TO	
0 PLC	±	-																						
1 PLC	±	-																						
2 PLC	±	-																						
3 PLC	±	0.25 [.010]																						
4 PLC	±	-																						
ANGLES	±	-																						
MATERIAL	SEE TABLE	FINISH	SEE TABLE	WEIGHT	-	SIZE	A2																	
CUSTOMER DRAWING		SCALE		4:1	SHEET	1 OF 2	REV	F																

1471-9 (3/11)


52119

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1	-	-	-

>PA<	BROWN	66/6 NYLON,VO	2	1-521119-7
>PA<	YELLOW	66/6 NYLON,VO	2	1-521119-6
>PA<	GREEN	66/6 NYLON,VO	2	1-521119-5
>PA<	BLACK	66/6 NYLON,VO	2	1-521119-4
>PA<	RED	66/6 NYLON,VO	2	1-521119-3
>PA<	BLUE	66/6 NYLON,VO	2	1-521119-2
>PA<	NATURAL	66/6 NYLON,VO		1-521119-1
>PA<	BROWN	6/6 NYLON,V2	2	1-521119-0
>PA<	YELLOW	6/6 NYLON,V2	2	521119-9
>PA<	GREEN	6/6 NYLON,V2	2	521119-8
>PA<	BLACK	6/6 NYLON,V2	2	521119-7
>PA<	RED	6/6 NYLON,V2	2	521119-6
>PA<	NATURAL	6/6 NYLON VO, GWT		521119-5
>PA<	BLUE			521119-4
>PA<	PUTTY	6/6 NYLON	6	521119-2
>PA<	NATURAL			521119-1
DFE SYMBOL	COLOR	MATERIAL	PART NO	

521119

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	7/3/96	 TE Connectivity																	
DIMENSIONS: mm [INCHES]		CHK	M FEHER	7/3/96																		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J GILLESPIE	7/3/96																		
<table border="0"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>0.25 [.010]</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-		1 PLC	±	-	2 PLC	±	-	3 PLC	±	0.25 [.010]	4 PLC	±	-	ANGLES	±	-	PRODUCT SPEC	
0 PLC	±	-																				
1 PLC	±	-																				
2 PLC	±	-																				
3 PLC	±	0.25 [.010]																				
4 PLC	±	-																				
ANGLES	±	-																				
MATERIAL SEE TABLE		FINISH SEE TABLE		APPLICATION SPEC	HOUSING, RECPT, POSITIVE-LOCK, MKIII, 2 CIRCUIT, 6.35 [.250] SERIES																	
WEIGHT		-		SIZE	A2																	
CUSTOMER DRAWING		SCALE		CAGE CODE	00779																	
SCALE		4:1		DRAWING NO	C=521119																	
SHEET		2 of 2		RESTRICTED TO	-																	
REV		F																				