



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	JASON KUNTZ	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-03-29	<b>Contact Email</b>	jp.kuntz@te.com				
<b>Contact Phone Number</b>	717-986-5932								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	4-1437565-1	<b>Amount</b>	277.0	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	FSM4JSMA=SM T,TACTILE,PB SWITCH	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUROHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	T/CASE				1.0	103.0	mg	
Substance	2	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	60.0	1.0	61.8	mg	N/A
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	41.2	mg	N/A
Material	1	COVER				1.0	52.0	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.1	1.0	0.052	mg	N/A
Substance	2	Copper	Supplier	7440-50-8	0.2	1.0	0.104	mg	N/A
Substance	2	Carbon	Supplier	7440-44-0	0.13	1.0	0.0676	mg	N/A
Substance	2	Iron	Supplier	7439-89-6	98.97	1.0	51.4644	mg	N/A
Substance	2	Manganese	Supplier	7439-96-5	0.6	1.0	0.312	mg	N/A
Material	1	D/ CONTACT				1.0	10.0	mg	
Substance	2	Copper	Supplier	7440-50-8	91.8	1.0	9.18	mg	N/A
Substance	2	Tin	Supplier	7440-31-5	8.0	1.0	0.8	mg	N/A
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.02	mg	N/A
Material	1	TERMINAL				1.0	75.0	mg	
Substance	2	Copper	Supplier	7440-50-8	70.0	1.0	52.5	mg	N/A
Substance	2	Zinc oxide (ZnO)	Supplier	1314-13-2	30.0	1.0	22.5	mg	N/A
Material	1	STEM				1.0	37.0	mg	
Substance	2	Antimonate (SbO3 <sup>1-</sup> ), sodium (1:1)	Supplier	15432-85-6	5.1	1.0	1.887	mg	N/A
Substance	2	Carbon black	Supplier	1333-86-4	0.2	1.0	0.074	mg	N/A
Substance	2	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	40.0	1.0	14.8	mg	N/A
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.7	1.0	0.259	mg	N/A
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	11.1	mg	N/A
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	24.0	1.0	8.88	mg	N/A