



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Philipp Harrer	Contact Title			
Company Unique ID	TE Connectivity	Response Date	2016-08-16	Contact Email	philipp.harrer@te.com				
Contact Phone Number	+432842905602817								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1393219-6	Amount	5.2482	Version	-	Identity			
Manufacturer Item Name	PE014012	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	PE16002---KAMM				1.0	0.0223	g	
Material	2	LCP-GF50				1.0	0.0223	g	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	4.46E-4	g	
Substance	3	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	48.0	1.0	0.010704	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	50.0	1.0	0.01115	g	
Sub-Item	1	PE72502---AK-TRAEGER + KT				1.0	0.0843	g	
Material	2	Copper				1.0	0.0572	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	2.86E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	5.72E-7	g	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.05706129	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.72E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	2.86E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.72E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.144E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.72E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.86E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.86E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.86E-6	g	
Material	2	AgNi10				1.0	0.0271	g	
Substance	3	Silver	Supplier	7440-22-4	37.86	1.0	0.01026006	g	
Substance	3	Copper	Supplier	7440-50-8	57.94	1.0	0.01570174	g	
Substance	3	Nickel, 5,5-(1,2-diazenediyl)bis[2,4,6-(1H,3H,5H)-pyrimidinetrionel] complexes	Supplier	68511-62-6	4.2	1.0	0.0011382	g	
Sub-Item	1	PE72503---UK-TRAEGER + FEDER				1.0	0.2463	g	
Material	2	Copper				1.0	0.146	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	7.3E-5	g	

Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	1.46E-6	g	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.14564595	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.46E-6	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	7.3E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	1.46E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	2.92E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.46E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	7.3E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.3E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	7.3E-6	g	
Material	2	Beryllium Copper				1.0	0.0673	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	6.73E-7	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.346E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.2	1.0	1.346E-4	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	1.0	1.346E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.5	1.0	3.365E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	1.0	4.038E-4	g	
Substance	3	Copper	Supplier	7440-50-8	98.1535	1.0	0.06605731	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	6.73E-6	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	6.73E-6	g	
Substance	3	Silicon	Supplier	7440-21-3	0.2	1.0	1.346E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	3.365E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.365E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	3.365E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	3.365E-5	g	
Material	2	AgNi10				1.0	0.033	g	
Substance	3	Nickel, 5,5-(1,2-diazenediyl)bis[2,4,6(1H,3H,5H)-pyrimidinetrione] complexes	Supplier	68511-62-6	10.0	1.0	0.0033	g	
Substance	3	Silver	Supplier	7440-22-4	90.0	1.0	0.0297	g	
Sub-Item	1	PE16005---KAPPE				1.0	0.4153	g	
Material	2	PA66-GF25-FR(17+72)				1.0	0.4153	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.5	1.0	0.0269945	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	0.103825	g	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.0	1.0	0.08306	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	38.0	1.0	0.157814	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.5	1.0	0.0103825	g	
Substance	3	Boron zinc oxide (B6Zn2O11)	Supplier	12767-90-7	8.0	1.0	0.033224	g	
Sub-Item	1	PE16004--B GRUNDPLATTE				1.0	0.1485	g	
Material	2	PBT-GF45				1.0	0.1485	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	0.066825	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.0	1.0	0.00891	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	8.0	1.0	0.01188	g	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	41.0	1.0	0.060885	g	
Sub-Item	1	PE16003--F GRUNDKOER PER				1.0	0.3572	g	
Material	2	PBT-GF45				1.0	0.3572	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	0.16074	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.0	1.0	0.021432	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	8.0	1.0	0.028576	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	41.0	1.0	0.146452	g	
Sub-Item	1	Adhesive and Sealants				1.0	0.05	g	
Material	2	Adhesive (unary)				1.0	0.05	g	
Substance	3	Phenol,4,4'-(1-methylethylidene)bis-, polymer with 2-(chloromethyl)oxirane, 2-propenoate	Supplier	55818-57-0	85.0	1.0	0.0425	g	
Substance	3	Methylamine	Supplier	74-89-5	15.0	1.0	0.0075	g	
Sub-Item	1	PE71012---MAGN.SYST. 12V DC				1.0	3.8287	g	
Material	2	Nickel Plate				1.0	0.012	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	2.4E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.2E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.011964	g	
Material	2	Iron Strip				1.0	2.082	g	
Substance	3	Vanadium	Supplier	7440-62-2	0.0070	1.0	1.4574E-4	g	
Substance	3	Silicon	Supplier	7440-21-3	0.15	1.0	0.003123	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	2.082E-4	g	
Substance	3	Titanium	Supplier	7440-32-6	0.0070	1.0	1.4574E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.36	1.0	0.0074952	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.09	1.0	0.0018738	g	
Substance	3	Copper	Supplier	7440-50-8	0.08	1.0	0.0016656	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.022	1.0	4.5804E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.082E-4	g	
Substance	3	Carbon	Supplier	7440-44-0	0.01	1.0	2.082E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.0012492	g	
Substance	3	Iron	Supplier	7439-89-6	98.8885	1.0	2.05885857	g	
Substance	3	Sulfur	Supplier	7704-34-9	0.022	1.0	4.5804E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.002082	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.082E-5	g	
Substance	3	Nitrogen	Supplier	7727-37-9	0.0070	1.0	1.4574E-4	g	
Substance	3	Nickel	Nickel	7440-02-0	0.07	1.0	0.0014574	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.041E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002082	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	1.041E-4	g	
Material	2	Copper Plate				1.0	0.012	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.2E-5	g	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	0.011988	g	
Material	2	LCP-GF50				1.0	0.2507	g	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	0.005014	g	

Substance	3	2-Naphthalenecarboxylic acid, 6-(acetyloxy)-, polymer with 4-(acetyloxy)benzoic acid	Supplier	70679-92-4	48.0	1.0	0.120336	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	50.0	1.0	0.12535	g	
Material	2	Copper				1.0	1.419	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	7.095E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	7.095E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	1.419E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	1.419E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.419E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	1.419E-4	g	
Substance	3	Copper	Supplier	7440-50-8	99.7625	1.0	1.41562988	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.001419	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	1.419E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	7.095E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.095E-6	g	
Material	2	Phos Bronze				1.0	0.053	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.3E-6	g	
Substance	3	Copper	Supplier	7440-50-8	91.9385	1.0	0.0487274	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	5.3E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.59E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.06E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.3E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.3E-5	g	
Substance	3	Tin	Supplier	7440-31-5	7.0	1.0	0.00371	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.855E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	1.0	7.95E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	5.3E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.65E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.65E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	5.3E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.65E-5	g	
Sub-Item	1	PE72501---RK-TRAEGER + KT				1.0	0.0956	g	
Material	2	Copper				1.0	0.0685	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	3.425E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	6.85E-7	g	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.06833389	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	6.85E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	3.425E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	6.85E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.37E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	6.85E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	3.425E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.425E-7	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	3.425E-6	g	
Material	2	AgNi10				1.0	0.0271	g	
Substance	3	Silver	Supplier	7440-22-4	37.86	1.0	0.01026006	g	
Substance	3	Copper	Supplier	7440-50-8	57.94	1.0	0.01570174	g	
Substance	3	Nickel, 5,5-(1,2-diazenediyl)bis[2,4,6-(1H,3H,5H)-pyrimidinetrione] complexes	Supplier	68511-62-6	4.2	1.0	0.0011382	g	