

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-18-009160	14JUN2018	DHC	SBH



VIEW A

NOTES:

- 1 PACKAGING: ACC. TO TE SPEC. 107-18032
- 2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.
SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- 3 WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE

WIRING SCHEDULE 3

CAVITY SIDE A	COLOR
1	WH/OG
2	OG
3	WH/GN
4	BU
5	WH/BU
6	GN
7	WH/BN
8	BN

10	HiFlex MultiPurpose 70°C PUR	2-2205129-6
5	HiFlex MultiPurpose 70°C PUR	2-2205129-5
3	HiFlex MultiPurpose 70°C PUR	2-2205129-4
2	HiFlex MultiPurpose 70°C PUR	2-2205129-3
1	HiFlex MultiPurpose 70°C PUR	2-2205129-2
0.5	HiFlex MultiPurpose 70°C PUR	2-2205129-1
10	HI 125°C TPE	1-2205129-6
5	HI 125°C TPE	1-2205129-5
3	HI 125°C TPE	1-2205129-4
2	HI 125°C TPE	1-2205129-3
1	HI 125°C TPE	1-2205129-2
0.5	HI 125°C TPE	1-2205129-1
10	STD 110°C PVC	-2205129-6
5	STD 110°C PVC	-2205129-5
3	STD 110°C PVC	-2205129-4
2	STD 110°C PVC	-2205129-3
1	STD 110°C PVC	-2205129-2
0.5	STD 110°C PVC	-2205129-1
Length/m	Cable version	TE PN

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2015 SATHISH KUMAR .G	TE Connectivity			
DIMENSIONS: mm		CHK 03FEB2015 B.VELDHOVEN				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 03FEB2015 A.VAN ZANDVOORT	NAME CA MINI IO TYPE I PIGTAIL			
		PRODUCT SPEC 108-78955	-			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 1°		APPLICATION SPEC 114-5506	-			
MATERIAL	FINISH	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-2205129	RESTRICTED TO
-	-	-	SCALE NTS		SHEET 1 OF 1	REV A2
CUSTOMER DRAWING						