



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-05-23	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	4-1614354-2	Amount	1.85	Version	-	Identity			
Manufacturer Item Name	RN 0603 68R1 0.1% 10PPM CUT LENGTH	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	G Mark				1.0	0.01	mg	
Substance	2	Ethanol, 2-butoxy-	Supplier	111-76-2	100.0	1.0	0.01	mg	N/A
Material	1	C1 paste				1.0	0.0215	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.0215	mg	N/A
Material	1	Tin plating				1.0	0.00945	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.00945	mg	N/A
Material	1	Ceramic				1.0	1.75	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	1.68	mg	N/A
Substance	2	Silica	Supplier	7631-86-9	4.0	1.0	0.07	mg	N/A
Material	1	Side Termination				1.0	5.0E-5	mg	
Substance	2	Nickel	Nickel	7440-02-0	50.0	1.0	2.5E-5	mg	N/A
Substance	2	Chromium	Supplier	7440-47-3	50.0	1.0	2.5E-5	mg	N/A
Material	1	C3 paste				1.0	0.0258	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	0.0258	mg	N/A
Material	1	Resistive Element				1.0	0.01185	mg	
Substance	2	Chromium	Supplier	7440-47-3	50.0	1.0	0.005925	mg	N/A
Substance	2	Nickel	Nickel	7440-02-0	50.0	1.0	0.005925	mg	N/A
Material	1	Nickel plating				1.0	0.00515	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.00515	mg	N/A
Material	1	G2 layer				1.0	0.0162	mg	
Substance	2	Propanoic acid, 2-methyl-, monoester with 2,2,4-trimethyl-1,3-pentanediol	Supplier	25265-77-4	100.0	1.0	0.0162	mg	N/A