





1. WILL ACCEPT (12) MULTIMATE AND (4) TYPE XII PIN CONTACTS.

2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.

3. NO. 4 FASTENERS RECOMMENDED FOR MOUNTING.

4. THIS CONNECTOR WILL ACCEPT INSULATION DIAMETERS UP TO 3.81 [.150].

5. HOUSING: NYLON, BLACK.

6. PERIPHERAL SEAL: ELASTOMER, GRAY.

7. PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY IDENTIFICATION.

8. HOUSING: NYLON, RED.

9. PERIPHERAL SEAL: ELASTOMER, GRAY.

10. WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

OBSOLETE	3	—	YES	A	1-207486-1
OBSOLETE	4	—	YES	A	207486-9
PRELIMINARY	5	—	YES	A	207486-7
	6	4	YES	A	207486-6
	7	—	YES	A	207486-5
	8	—	NO	B	207486-2
	9	—	NO	A	207486-1
NOTES	THREADED INSERTS	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN M. BINNER 05/26/94

CHK R. STONE 6-23-94

APVD -

PRODUCT SPEC 108-10024

APPLICATION SPEC -

WEIGHT -

SIZE A1

CAGE CODE 00779

DRAWING NO. 207486

RESTRICTED TO -

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV R

TE Connectivity

RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC

-