



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-05-23	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	7-1879254-0	Amount	9.02	Version	-	Identity			
Manufacturer Item Name	RP 2B 40R2 0.1% 15PPM CUT LENGTH	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Overcoat				1.0	0.0822	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	0.009864	mg	
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	0.002466	mg	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	0.02877	mg	
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	0.01644	mg	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	0.00822	mg	
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	0.01644	mg	
Material	1	Nickel Plating				1.0	0.024	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.024	mg	
Material	1	Resistor Layer				1.0	3.3E-5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	3.3E-5	mg	
Material	1	Substrate				1.0	8.6088252	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	8.26447	mg	
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	3.0	1.0	0.25826	mg	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	0.08608825	mg	
Material	1	Backside Electrode				1.0	0.103	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.0206	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0103	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.01545	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.05665	mg	
Material	1	Tin Plating				1.0	0.0554	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.0554	mg	
Material	1	Upside Electrode				1.0	0.103	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.0206	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0103	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.01545	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.05665	mg	
Material	1	Marking				1.0	0.0435	mg	

Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	20.0	1.0	0.0087	mg	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	80.0	1.0	0.0348	mg	
Material	1	Edge Electrode				1.0	4.18E-5	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	4.18E-5	mg	