



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2017-03-21	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	3-794633-6	Amount	949.424286	Version	-	Identity																												
Manufacturer Item Name	06P MICRO MNL ASSY,VRT,SMT, LF	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	MICROMNL LP CONT,VERT,P RE-TIN				2.0	115.811143	mg																										
Material	2	Phos Bronze				2.0	112.453	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.11245	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0112453	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.2	2.0	0.22491	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.00562265	mg																										
Substance	3	Copper	Supplier	7440-50-8	90.0485	2.0	101.26224	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0224906	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.39359	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00112453	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.11245	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0112453	mg																										
Substance	3	Tin	Supplier	7440-31-5	9.0	2.0	10.12077	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.11245	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	5.6226E-4	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00562265	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0562265	mg																										
Material	2	Tin Plate				2.0	2.115	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	2.10929	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00423	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.0014805	mg																										
Material	2	Nickel Plate				2.0	1.243143	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00248629	mg																										

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00124314	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.23941	mg	
Sub-Item	1	Kapton Dot - Vacuum pickup button .055T				1.0	8.0	mg	
Material	2	Polyester				1.0	8.0	mg	
Substance	3	Siloxanes and Silicones, di-Me, reaction products with silica	Supplier	67762-90-7	55.0	1.0	4.4	mg	
Substance	3	1H,3H-Benzo[1,2-c:4,5-c']difuran-1,3,5,7-tetrone, polymer with 4,4-oxybis[benzen amine]	Supplier	25038-81-7	45.0	1.0	3.6	mg	
Sub-Item	1	MICROMNL LP CONT,VERTICLE,SN				6.0	42.137	mg	
Material	2	Brass				6.0	41.32	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	4.132E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	6.0	11.5789	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.02066	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.004132	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.02066	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.04132	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	6.0	29.5438	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	4.132E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.004132	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	2.066E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.08264	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	0.002066	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.02066	mg	
Material	2	Tin Plate				6.0	0.561	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	6.0	0.55949	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.001122	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	3.927E-4	mg	
Material	2	Nickel Plate				6.0	0.256	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	5.12E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	2.56E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.25523	mg	
Sub-Item	1	6POS MICRO MNL HSG,BLACK				1.0	456.98	mg	
Material	2	PA4T-GF30-FR(40)				1.0	456.98	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	4.11282	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	137.094	mg	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	215.23758	mg	
Substance	3	Halogen-free organic phosphorus flame retardant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	54.8376	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	45.698	mg	