



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer, Eng Proc Opt/LEANPD		
Company Unique ID	TE Connectivity	Response Date	2017-03-11	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	554085-1	Amount	17281.356548	Version	-	Identity			
Manufacturer Item Name	PLUG ASSY,50 POS,BAIL LOCK,LPF	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SUPPORT/TE RM,PLUG,LPF ,C/LATCH				1.0	1297.8	mg	
Material	2	PPE+PS				1.0	1297.8	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	25.956	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	535.01805	mg	
Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	155.736	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	1.9467	mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supplier	25448-25-3	1.0	1.0	12.978	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	1.9467	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	1.9467	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	12.978	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	1.2978	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	12.978	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	535.01805	mg	
Sub-Item	1	COVER, .050/.085, CHAMP				1.0	3563.0	mg	
Material	2	PBT-GF15				1.0	3563.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	53.445	mg	

Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	17.815	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	14.252	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	1991.717	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	178.15	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	106.89	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	32.067	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	17.815	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	605.71	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	10.689	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	534.45	mg	
Sub-Item	1	CAP, TERM HSG, .050/.085				1.0	1225.8	mg	
Material	2	PPE+PS				1.0	1225.8	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	24.516	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	505.33605	mg	
Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	147.096	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	1.8387	mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supplier	25448-25-3	1.0	1.0	12.258	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	1.8387	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	1.8387	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	12.258	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	1.2258	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	12.258	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	505.33605	mg	
Sub-Item	1	TERMINAL, AR RAY, 50POS, C HAMP-LCH				1.0	1920.128171	mg	
Material	2	Nickel Plate				1.0	20.026245	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04005249	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02002625	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	19.96617	mg	
Material	2	Copper Alloy				1.0	1898.5	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.8985	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	3.797	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.5	1.0	9.4925	mg	
Substance	3	Copper	Supplier	7440-50-8	85.2175	1.0	1617.85424	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.018985	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.018985	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.18985	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	11.391	mg	
Substance	3	Tin	Supplier	7440-31-5	2.8	1.0	53.158	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.18985	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.18985	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.5	1.0	199.3425	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0094925	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.94925	mg	
Material	2	Gold Plate				1.0	0.191	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	5.73E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.19043	mg	
Material	2	Gold Plate				1.0	1.410926	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	1.39682	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	0.01410926	mg	
Sub-Item	1	TERMINAL, AR RAY, 50 POS, CHAMP-LCH				1.0	1920.128377	mg	
Material	2	Nickel Plate				1.0	20.026245	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04005249	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02002625	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	19.96617	mg	
Material	2	Copper Alloy				1.0	1898.5	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.8985	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	3.797	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.5	1.0	9.4925	mg	
Substance	3	Copper	Supplier	7440-50-8	85.2175	1.0	1617.85424	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.018985	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.018985	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.18985	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	11.391	mg	
Substance	3	Tin	Supplier	7440-31-5	2.8	1.0	53.158	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.18985	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.18985	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.5	1.0	199.3425	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0094925	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.94925	mg	
Material	2	Gold Plate				1.0	0.191206	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	5.7362E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.19063	mg	
Material	2	Gold Plate				1.0	1.410926	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	1.39682	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	0.01410926	mg	
Sub-Item	1	HSG, PLUG, BALL LOCK, CHAMP LATCH				1.0	7354.5	mg	
Material	2	PPE+PS				1.0	7354.5	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	147.09	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	3031.89262	mg	

Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	882.54	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	11.03175	mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supplier	25448-25-3	1.0	1.0	73.545	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	11.03175	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	11.03175	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	73.545	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	7.3545	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	73.545	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	3031.89262	mg	