



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John Penica	Contact Title	Sr. Manager- Global Product Environmental Compliance																											
Company Unique ID	TE Connectivity	Response Date	2017-02-22	Contact Email	jrpenica@te.com																													
Contact Phone Number		1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	8-31880-1	Amount	0.71214208	Version	-	Identity																												
Manufacturer Item Name	PIDG R 22-16 COMM 22-18 MIL 4	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	BUDG R 22-16 COMM 22-18 MIL 4				1.0	0.42256803	g																										
Material	2	Tin Plate				1.0	0.00446803	g																										
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.00445597	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	8.936062E-6	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	3.127622E-6	g																										
Material	2	Copper				1.0	0.4181	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	2.0905E-4	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.0905E-4	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	4.181E-6	g																										
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.41708611	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.181E-6	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	4.181E-5	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	2.0905E-5	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	8.362E-5	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	4.181E-4	g																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.0905E-6	g																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.0905E-5	g																										
Sub-Item	1	SLEEVE ASSEMBLY 22-16				1.0	0.28957405	g																										
Material	2	Tin Plate				1.0	0.00423	g																										
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.00421858	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	8.46E-6	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	2.961E-6	g																										
Material	2	COLORANT				1.0	0.00155808	g																										

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	1.402273E-5	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	96.4	1.0	0.00150199	g	
Substance	3	9,10-Anthracenedione, 1-(methylamino)-	Supplier	82-38-2	2.7	1.0	4.206819E-5	g	
Material	2	PA66				1.0	0.07634597	g	
Substance	3	Phosphoric acid	Supplier	7664-38-2	0.075	1.0	5.725948E-5	g	
Substance	3	Acetic acid	Supplier	64-19-7	0.015	1.0	1.14519E-5	g	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	89.39	1.0	0.06824566	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.0076346	g	
Substance	3	Acetic acid, copper(2) salt (2:1)	Supplier	142-71-2	0.02	1.0	1.526919E-5	g	
Substance	3	Potassium bromide	Supplier	7758-02-3	0.5	1.0	3.8173E-4	g	
Material	2	Copper				1.0	0.20744	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.0372E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.0372E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.0744E-6	g	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.20693696	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.0744E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.0744E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	1.0372E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	4.1488E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.0744E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.0372E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	1.0372E-5	g	