



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2017-07-24	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2199070-4	Amount	166.064	Version	-	Identity			
Manufacturer Item Name	0.5MM FPH BTB, 4H/24POS/15U/ TR/WOB	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	0.5mm FS BTB, 4H/HERMAPH RODITIC/15U				1.0	166.064	mg	
Material	2	Copper Alloy				1.0	45.6	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0228	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.0	1.0	0.456	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.2	1.0	0.5472	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0456	mg	
Substance	3	Copper	Supplier	7440-50-8	92.7685	1.0	42.30244	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.06	1.0	0.02736	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.56E-4	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	1.0	0.1368	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	1.0	0.0456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	1.0	0.0912	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.00228	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00456	mg	
Substance	3	Nickel	Nickel	7440-02-0	4.2	1.0	1.9152	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00228	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.28E-4	mg	
Material	2	LCP-GF30				1.0	34.0	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	5.0	1.0	1.7	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	0.068	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.1	1.0	9.894	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.9	1.0	0.306	mg	

Substance	3	2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarb oxylic acid, 1,4-benzenediol, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoi c acid	Supplier	126710-21-2	64.8	1.0	22.032	mg	
Material	2	Gold Plate				1.0	0.12	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.11964	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	3.6E-4	mg	
Material	2	LCP				1.0	85.0	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	14.0	1.0	11.9	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	1.8	1.0	1.53	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.4	1.0	0.34	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.2	1.0	0.17	mg	
Substance	3	Aluminum hydroxide (Al(OH)3)	Supplier	21645-51-2	0.23	1.0	0.1955	mg	
Substance	3	Silica	Supplier	7631-86-9	0.12	1.0	0.102	mg	
Substance	3	2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarb oxylic acid, 1,4-benzenediol and 4-hydroxybenzoi c acid	Supplier	86013-04-9	57.7	1.0	49.045	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.15	1.0	0.1275	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	5.6	1.0	4.76	mg	
Substance	3	Magnesite (Mg(CO3)), calcined	Supplier	83897-85-2	0.2	1.0	0.17	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.6	1.0	16.66	mg	
Material	2	Nickel Plate				1.0	1.344	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001344	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.002688	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.33997	mg	