



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-06-05	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5227754-3	Amount	7664.077569	Version	-	Identity			
Manufacturer Item Name	BNC SOLDER RECEPT JACK	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	JAM NUT				1.0	2527.979168	mg	
Material	2	Nickel Plate				1.0	7.979168	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00797917	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	7.95523	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01595834	mg	
Material	2	Brass				1.0	2520.0	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0252	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.252	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.52	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.252	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.504	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0252	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	8.82	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	825.237	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	1587.6	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0126	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.252	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	93.24	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.26	mg	
Sub-Item	1	LOCK WASHER COAXICON				1.0	176.13273	mg	
Material	2	Stainless Steel				1.0	172.3	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	8.615E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.75	1.0	1.29225	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.25845	mg	

Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.001723	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.05169	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	1.0	0.06892	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.0	1.0	1.723	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01723	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	1.0	1.723	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.01723	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.1723	mg	
Substance	3	Chromium	Supplier	7440-47-3	13.5	1.0	23.2605	mg	
Substance	3	Iron	Supplier	7439-89-6	83.3035	1.0	143.53193	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.1723	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.008615	mg	
Material	2	Nickel Plate				1.0	3.83273	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00383273	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	3.82123	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00766546	mg	
Sub-Item	1	BNC JACK ASS'Y				1.0	4959.965671	mg	
Material	2	Zinc Alloy				1.0	3801.3	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	1.33046	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	0.76026	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0030	1.0	0.11404	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.06	1.0	2.28078	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	9.50325	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.38013	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.0315	1.0	3612.43241	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	163.4559	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.38013	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.038013	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	3.8013	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.8013	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	1.90065	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	0.76026	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	0.19007	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0190065	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	1.0	0.15205	mg	
Material	2	Nickel Plate				1.0	43.815	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.043815	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	43.68356	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.08763	mg	
Material	2	Copper Plate				1.0	69.298671	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.06929867	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	69.22937	mg	
Material	2	PBT-GF15				1.0	550.7	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	4.9563	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.5	1.0	13.7675	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	27.535	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	0.5507	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	1.6521	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	2.7535	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	57.8	1.0	318.3046	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	2.2028	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[1-(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	2.7535	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	93.619	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	15.0	1.0	82.605	mg	
Material	2	Phos Bronze				1.0	469.3	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	444.42006	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.09386	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.04693	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	21.1185	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.023465	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.4693	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.04693	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.004693	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.4079	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.4693	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.4693	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.023465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.23465	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.4693	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0023465	mg	
Material	2	Silver Plate				1.0	25.552	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.51104	mg	
Substance	3	Silver	Supplier	7440-22-4	98.0	1.0	25.04096	mg	