



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2017-08-09	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5749621-5	Amount	6832.243275	Version	-	Identity																												
Manufacturer Item Name	50 50S CABLE PLUG CONN/COV KIT	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	50 50SR CABLE PLUG SUB-ASSY				1.0	5898.243275	mg																										
Material	2	Carbon Steel				1.0	2701.4685	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01350734	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.27015	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	16.20881	mg																										
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	3.51191	mg																										
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	1.08059	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.0522	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.02701469	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.54029	mg																										
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.70147	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.70147	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.26745	mg																										
Substance	3	Iron	Supplier	7439-89-6	98.6837	1.0	2665.90907	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	2.69877	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.13507	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.35073	mg																										
Material	2	Phos Bronze				1.0	1537.5	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	1455.98944	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.3075	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.15375	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	69.1875	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.076875	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	1.5375	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.15375	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.015375	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	4.6125	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	1.5375	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.5375	mg																										

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.076875	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.76875	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	1.5375	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0076875	mg	
Material	2	Tin Plate				1.0	19.05635	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0381127	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	19.0049	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.01333945	mg	
Material	2	Nickel Plate				1.0	20.368225	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04073645	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02036823	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	20.30712	mg	
Material	2	Copper Plate				1.0	30.6985	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0306985	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	30.6678	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	1520.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	7.6	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	532.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	3.04	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	3.04	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	45.6	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	30.4	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	15.2	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	7.6	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	15.2	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	556.32	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	7.6	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	273.6	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	7.6	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	15.2	mg	
Material	2	Gold Plate				1.0	2.495	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	2.48752	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.007485	mg	
Material	2	Nickel Plate				1.0	61.2595	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0612595	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	61.07572	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.12252	mg	
Material	2	Tin-Nickel Plate				1.0	5.3972	mg	
Substance	3	Tin	Supplier	7440-31-5	70.0	1.0	3.77804	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	0.026986	mg	
Substance	3	Nickel	Nickel	7440-02-0	29.5	1.0	1.59217	mg	
Sub-Item	1	50 50SR CBL CONN TERM COVER				2.0	467.0	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	467.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	2.335	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	163.45	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.934	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.934	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	14.01	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	2.0	9.34	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	4.67	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	2.335	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	4.67	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	170.922	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	2.335	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	84.06	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	2.0	2.335	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	2.0	4.67	mg	