



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-06-21	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	9-1393640-2	Amount	21341.1968	Version	-	Identity			
Manufacturer Item Name	V42254B2201C9 60=PC612 FEDERLEI	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	C23334A1004 C102H=KT GEV LOET K				96.0	78.6583	mg	
Material	2	Gold Plate				96.0	0.015	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	96.0	0.01485	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	96.0	1.5E-4	mg	
Material	2	Phos Bronze				96.0	63.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	96.0	59.66005	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	96.0	0.0126	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	96.0	0.0063	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	96.0	2.835	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	96.0	0.00315	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	96.0	0.063	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	96.0	0.0063	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	96.0	6.3E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	96.0	0.189	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	96.0	0.063	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	96.0	0.063	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	96.0	0.00315	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	96.0	0.0315	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	96.0	0.063	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	96.0	3.15E-4	mg	
Material	2	Nickel Plate				96.0	12.672	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	96.0	0.012672	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	96.0	12.63398	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	96.0	0.025344	mg	
Material	2	112-65				96.0	2.9413	mg	

Substance	3	Tin	Supplier	7440-31-5	99.73	96.0	2.93336	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	96.0	0.0058826	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	96.0	0.00205891	mg	
Material	2	Palladium-Nickel Plate				96.0	0.03	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	96.0	0.024	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	96.0	0.0060	mg	
Sub-Item	1	C23334A1004 C831 X97=KS ONDERDE				1.0	6687.0	mg	
Material	2	PBT-GF30-FR(17)				1.0	6687.0	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.2	1.0	13.374	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	2006.1	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.2	1.0	80.244	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.6	1.0	240.732	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	55.0	1.0	3677.85	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.2	1.0	13.374	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	20.061	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	9.5	1.0	635.265	mg	
Sub-Item	1	C23334A1004 C431 X97=KS BOVENDE				1.0	7103.0	mg	
Material	2	PBT-GF30-FR(17)				1.0	7103.0	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.2	1.0	14.206	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	2130.9	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.2	1.0	85.236	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.6	1.0	255.708	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	55.0	1.0	3906.65	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	0.2	1.0	14.206	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	21.309	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	9.5	1.0	674.785	mg	