


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	B1	ECR-07-020339		30AUG2007	RC	MS	



NOTES:

- CPR IS 16dB ACCORDING TO IEEE DRAFT P802.3Z/D5.0
- ATTENUATION $\leq 0,3\text{dB}$, MEASURED AT 1300nm ACC. IEC 61300-3-4 METHOD B
- FILLED OUT TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- INDIVIDUAL LENGTH DIFFERENCE ON ST SIDE $\leq 50\text{mm}$ AND ON SC SIDE $\leq 5\text{mm}$
- TEXT ON CABLE LABEL: "TO CABLE PLANT"
- INFORMATION ON CABLE LABEL:
 - F.O. NUMBER
 - PRODUCTION DATE
- TEXT ON CABLE LABEL: "MODE CONDITIONING CABLE ASSEMBLY"
- INFORMATION ON CABLE LABEL:
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER
 - MANUFACTURING LOCATION
 - PRODUCTION DATE
- TEXT ON CABLE LABEL: "TO EQUIPMENT"

PART NUMBER	"L" (meter)
6348269-2	2,2 -0/+0,1
6348269-3	3,2 -0/+0,1
6348269-4	4,2 -0/+0,1
6348269-5	5,2 -0/+0,1
6348269-6	6,2 -0/+0,1
6348269-7	7,2 -0/+0,1
6348269-8	8,2 -0/+0,1
6348269-9	9,2 -0/+0,1
1-6348269-0	10,2 -0/+0,1

5	FOAC CABLE LABEL	6
1	SC CONNECTOR SINGLE MODE, DUPLEX HOUSING, BLUE	5
1	SC CONNECTOR MULTI MODE, DUPLEX HOUSING, BEIGE	4
2	ST CONNECTOR MULTI MODE	3
1	CPR SLEEVE	2
1	FOCAB 2,5TZ 50/125 ORANGE LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 24FEB2006	Tyco Electronics Corporation 's-Hertogenbosch, Netherlands	
DIMENSIONS: mm		CHK A. HENGELMOLEN 24FEB2006	NAME FOGBIT50 MCLL 2,5TZ 2x ST/PC - SC/PC DUPLEX	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD T. vd. MEULEN 24FEB2006	PRODUCT SPEC 108-19168	
MATERIAL		FINISH	WEIGHT	SCALE A2 00779 C=6348269
		CUSTOMER DRAWING		RESTRICTED TO SHEET 1 of 1 REV B1

6348269