



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R Penica	Contact Title	Sr Mgr Environmental Engineering																											
Company Unique ID	TE Connectivity	Response Date	2017-05-04	Contact Email	jrpenica@te.com																													
Contact Phone Number		+1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1622488-1	Amount	0.20548	Version	-	Identity																												
Manufacturer Item Name	LR1 1% 47K	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Resistor film				1.0	5.9E-4	g																										
Substance	2	Nickel	Nickel	7440-02-0	30.52	1.0	1.8007E-4	g																										
Substance	2	Aluminum	Supplier	7429-90-5	11.03	1.0	6.5077E-5	g																										
Substance	2	Chromium	Supplier	7440-47-3	58.45	1.0	3.4485E-4	g																										
Material	1	Insulation Coating				1.0	0.061494	g																										
Substance	2	Oxirane, 2,2-[[1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis-, homopolymer	Supplier	25085-99-8	82.0	1.0	0.05042508	g																										
Substance	2	Carbonic acid calcium salt (1:1)	Supplier	471-34-1	3.0	1.0	0.00184482	g																										
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	15.0	1.0	0.0092241	g																										
Material	1	Ceramic Core				1.0	0.036006	g																										
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	72.55	1.0	0.02612235	g																										
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	21.57	1.0	0.00776649	g																										
Substance	2	Barium oxide (BaO)	Supplier	1304-28-5	5.88	1.0	0.00211715	g																										
Material	1	End Cap				1.0	0.01459	g																										
Substance	2	Tin	Supplier	7440-31-5	9.67	1.0	0.00141085	g																										
Substance	2	Iron	Supplier	7439-89-6	78.37	1.0	0.01143418	g																										
Substance	2	Copper	Supplier	7440-50-8	11.96	1.0	0.00174496	g																										
Material	1	Color code				1.0	0.0010	g																										
Substance	2	Oxirane, 2,2-[[1-methylethylidene)bis(4,1-phenyleneoxy methylene)]bis-, homopolymer	Supplier	25085-99-8	74.9	1.0	7.49E-4	g																										
Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	25.1	1.0	2.51E-4	g																										
Material	1	Lead wire				1.0	0.0918	g																										
Substance	2	Copper	Supplier	7440-50-8	100.0	1.0	0.0918	g																										