


Sep.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	DIS-C-000490	T.H.E.K		07.01.31					



- NOTES
- ① TOTAL LENGTH BECOMES 28.8±1 WHEN ⑥ IS SCREWED INTO ① COMPLETERY.
  - ② THE RECOMMENDED CLUMP TORQUE OF REF. NO.⑥ TO BE 0.5N·m.  
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO.⑥ FROM LOOSENING.  
SPACER FOR ASSEMBLY IS AVAILABLE HR30-6P-T02.
  - ③ TABLE FOR ASSEMBLY AND SOLDERING IS AVAILABLE HR30-6R-6P-T01.
  - ④ SURFACE PLATING: GOLD PLATING 0.2μm min.  
UNDER PLATING: NICKEL PLATING 2μm min.
  - ⑤ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

3	PPS	(BLACK)	UL94V-0	6	PBT	(BLACK)	UL94V-0
2	BRASS	④		5	CR	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M.HANYU	H.NAGANO	E.KUNII	M.SATO	
	'05. 8 . 8	'05. 8 . 8	'05. 8 . 10	'05. 8 . 10	

 SCALE 5 : 1 UNITS mm	DRAWING NO. EDC3-112570-71 <b>HRS</b> HIROSE ELECTRIC CO., LTD	PART NO. HR30-6JA-6P(71) CODE NO. CL130-2018-7-71	1/1
-----------------------------------	---	--	-----

TO
R