

**DESIGNED & DIMENSIONED
IN MILLIMETERS**

*POWER POSITIONS (PER END)
-01, -02, ***-03, ***-04

*SIGNAL POSITIONS

$$\begin{array}{l} ***-04: (4 \times 1) \\ ***-08: (4 \times 2) \\ ***-12: (4 \times 3) \\ -16: (4 \times 4) \\ ***-20: (4 \times 5) \\ -24: (4 \times 6) \\ -80: (4 \times 20) \end{array}$$

* POWER POSITIONS
(PER END)
***-00, -01, -02

LEADSTYLE
-01

OPTION (SEE NOTE 6)
-SD: SCREW DOWN
(SEE FIG 1, SHT 1)
-LC: LOCKING CLIP
(SEE FIG 2, SHT 2)

— RIGHT ANGLE

PLATING SPECIFICATION

-L: SEE TABLE 3
-T: SEE TABLE 3

— TAIL LENGTH

-01: FOR 1.57[.062] THICK PCB
(USE SUB-T-1M40-01-X)
-03: FOR 2.36[.093] THICK PCB
(USE SUB-T-1M40-03-X)

* SEE TABLE 2 FOR AVAILABLE COMBINATIONS
*** NOT RELEASED FOR PRODUCTION






FIG 1
MPTC-01-80-01-XX-X-RA-SD SHOWN

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES ARE:

DECIMALS	ANGLES
.X: ± 0.3 [.01]	2°
.XX: ± 0.13 [.005]	
.XXX: ± 0.051 [.0020]	

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: LCP, UL 94 V0, COLOR: BLACK
TERMINAL: COPPER ALLOY
LOCKING CLIP: COPPER ALLOY

SHEET SCALE: 1.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:	
--------------	--

RIGHT ANGLE POWER TERMINAL

DWG. NO.

MPTC-XX-XX-XX-01-XX-X-RA-XX

BY: CLAY W 2/2/2007

SHEET 1 OF 4

TABLE 3

PLATING	POWER PIN CONTACT AREA	POWER PIN TAIL	SIGNAL PIN CONTACT AREA	SIGNAL PIN TAIL
-L	10µ" GOLD	MATTE TIN	10µ" GOLD	MATTE TIN
-T	MATTE TIN	MATTE TIN	10µ" GOLD	MATTE TIN

TABLE 1								
PART NUMBER	BODY	SPACER BODY	POWER TERMINAL SUB-ASSEMBLY	SIGNAL TERMINAL				"A"
MPTC-XX-XX-XX-01-01-X-RA-XX	MPT-XX-RA-XX-XX	MP-XX-Q	SUB-T-1M40-01-X	TERMINAL 1	TERMINAL 2	TERMINAL 3	TERMINAL 4	2.72 [0.107]
MPTC-XX-XX-XX-01-03-X-RA-XX			SUB-T-1M40-03-X	T-1S68-01-L	T-1S68-02-L	T-1S68-03-L	T-1S68-04-L	3.51 [0.138]

TABLE 2									
PART NUMBER	BODY	"B"	"C"	"D"	"E"	"F"	"G"	"H"	"J"
MPTC-01-80-01-01-XX-X-RA-XX	MPT-02-RA-80-XX	63.25 [2.490]	58.17 [2.290]	46.88 [1.846]	48.77 [1.920]	54.26 [2.136]	38.00 [1.496]	59.44 [2.340]	41.40 [1.630]
MPTC-02-80-02-01-XX-X-RA-XX	MPT-04-RA-80-XX	73.25 [2.884]	68.17 [2.684]	56.88 [2.239]	58.77 [2.314]	64.26 [2.530]	38.00 [1.496]	69.44 [2.734]	41.40 [1.630]
MPTC-01-24-01-01-XX-X-RA-XX	MPT-02-RA-24-XX	35.25 [1.388]	30.17 [1.188]	18.88 [0.743]	20.77 [0.818]	26.26 [1.034]	10.00 [0.394]	31.44 [1.238]	13.40 [0.528]
MPTC-02-24-02-01-XX-X-RA-XX	MPT-04-RA-24-XX	45.25 [1.781]	40.17 [1.581]	28.88 [1.137]	30.77 [1.211]	38.01 [1.496]	10.00 [0.394]	41.44 [1.631]	13.40 [0.528]
MPTC-02-16-02-01-XX-X-RA-XX	MPT-04-RA-16-XX	41.25 [1.624]	36.17 [1.424]	24.88 [0.980]	26.77 [1.054]	32.26 [1.270]	6.00 [0.236]	37.44 [1.474]	9.40 [0.370]
MPTC-01-16-01-01-XX-X-RA-XX	MPT-02-RA-16-XX	31.25 [1.230]	26.17 [1.030]	14.88 [0.586]	16.77 [0.660]	22.26 [0.876]	6.00 [0.236]	27.44 [1.080]	9.40 [0.370]
***MPTC-01-08-01-01-XX-X-RA-XX	MPT-02-RA-08-XX	27.25 [1.073]	22.17 [0.873]	10.88 [0.428]	12.77 [0.503]	18.26 [0.719]	2.00 [0.079]	23.44 [0.923]	5.40 [0.213]
***MPTC-01-04-01-01-XX-X-RA-XX	MPT-02-RA-04-XX	25.25 [0.994]	20.17 [0.794]	8.88 [0.350]	10.77 [0.424]	16.26 [0.640]	N/A	21.44 [0.844]	3.40 [0.134]
***MPTC-03-24-00-01-XX-X-RA-XX	MPT-03-RA-24-XX-PS	41.25 [1.624]	36.17 [1.424]	N/A	N/A	32.26 [1.270]	10.00 [0.394]	37.44 [1.474]	13.40 [0.528]
***MPTC-04-24-00-01-XX-X-RA-XX	MPT-04-RA-24-XX-PS	46.25 [1.821]	41.17 [1.621]	N/A	N/A	37.26 [1.467]	10.00 [0.394]	42.44 [1.671]	13.40 [0.528]
***MPTC-03-20-00-01-XX-X-RA-XX	MPT-03-RA-20-XX-PS	39.25 [1.545]	34.17 [1.345]	N/A	N/A	30.26 [1.191]	8.00 [0.315]	35.44 [1.395]	11.40 [0.449]
***MPTC-04-20-00-01-XX-X-RA-XX	MPT-04-RA-20-XX-PS	44.25 [1.742]	39.17 [1.542]	N/A	N/A	35.26 [1.388]	8.00 [0.315]	40.44 [1.592]	11.40 [0.449]
***MPTC-03-16-00-01-XX-X-RA-XX	MPT-03-RA-16-XX-PS	37.25 [1.467]	32.17 [1.267]	N/A	N/A	28.26 [1.113]	6.00 [0.236]	33.44 [1.317]	9.40 [0.370]
***MPTC-04-16-00-01-XX-X-RA-XX	MPT-04-RA-16-XX-PS	42.25 [1.663]	37.17 [1.463]	N/A	N/A	33.26 [1.309]	6.00 [0.236]	38.44 [1.513]	9.40 [0.370]
***MPTC-03-12-00-01-XX-X-RA-XX	MPT-03-RA-12-XX-PS	35.25 [1.388]	30.17 [1.188]	N/A	N/A	26.26 [1.034]	4.00 [0.157]	31.44 [1.238]	7.40 [0.291]
***MPTC-04-12-00-01-XX-X-RA-XX	MPT-04-RA-12-XX-PS	40.25 [1.585]	35.17 [1.385]	N/A	N/A	31.26 [1.231]	4.00 [0.157]	36.44 [1.435]	7.40 [0.291]

*** = NOT RELEASED







FIG 2
MPTC-01-80-01-01-XX-X-RA-LC SHOWN
(SAME AS FIG 1, UNLESS OTHERWISE STATED)



0.25 [0.010] REF



SECTION "B"-"B"
SCALE 3 : 1

• PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

samtec

520 PARK EAST BLVD. NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:




RIGHT ANGLE POWER TERMINAL

DWG. NO.

MPTC-XX-XX-XX-01-XX-X-RA-XX

BY: CLAY W 2/2/2007

SHEET 2 OF 4



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION:
RIGHT ANGLE POWER TERMINAL

DWG. NO.
MPTC-XX-XX-XX-01-XX-X-RA-XX


BY: CLAY W 2/2/2007 SHEET 3 OF 4




IN-PROCESS 3
FILL T-1S68-XX-X ROW 2




IN-PROCESS 2
BEND ROW 1




IN-PROCESS 3
FILL T-1S68-XX-X ROW 2




IN-PROCESS 4
BEND ROW 2




IN-PROCESS 5
FILL T-1S68-XX-X ROW 3




IN-PROCESS 6
BEND ROW 3




IN-PROCESS 7
FILL T-1S68-XX-X ROW 4




IN-PROCESS 8
BEND ROW 4



IN-PROCESS 9
ADD MP-XX-Q



IN-PROCESS 10
SHEAR
(FOR -03 TAIL LENGTH ONLY)



IN-PROCESS 11
FILL SUB-T-1M40-XX-X

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
RIGHT ANGLE POWER TERMINAL

DWG. NO.
MPTC-XX-XX-XX-01-XX-X-RA-XX

BY: CLAY W 2/2/2007 SHEET 4 OF 4