



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china		
Company Unique ID	TE Connectivity	Response Date	2017-08-27	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	644753-2	Amount	631.564	Version	-	Identity			
Manufacturer Item Name	02P MTA156 HDR ASSY RN STR F/L	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Polyester Compound				1.0	361.9	mg	
Material	2	PBT-GF7				1.0	361.9	mg	
Substance	3	4,4'-isopropylidene diphenol (bisphenol A; BPA)	Supplier	80-05-7	0.01	1.0	0.03619	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	6.5	1.0	23.5235	mg	
Substance	3	Carbonic dichloride, polymer with 4,4'-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4'-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	108.57	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	28.952	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	3.619	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.49	1.0	197.19931	mg	
Sub-Item	1	Brass Round				1.0	269.664	mg	
Material	2	Nickel Plate				1.0	1.236	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.002472	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.001236	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	1.23229	mg	
Material	2	Brass Wire				1.0	266.4	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	190.476	mg	

Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.002664	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	74.65221	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.1332	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.002664	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.1332	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.2664	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.0263736	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.02664	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1332	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01332	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001332	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.5328	mg	
Material	2	Tin Plate				1.0	2.028	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.004056	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	2.02252	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0014196	mg	