



- 1 CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- 2 NYLON, UL 94V-0 RATED, BLACK.
- 3 CONTACT BODY: 0.76um[.000030] MIN GOLD FOR LENGTH OF 5.08[.200] MIN FROM MATING END, WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
- 4 CONTACT BODY: 2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
- 5 CONTACT BODY: 0.76um[.000030] MIN GOLD FOR LENGTH OF 5.08[.200] MIN FROM MATING END, WITH REMAINDER TO BE GOLD FLASH, BOTH OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 6 CONTACT BODY: 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL. CONTACT POST: 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 7 PRELIMINARY PART NUMBER.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7	14.22[.560]	4-40 UNC, INSERT, BRASS	5	1-213729-0
	9.35[.368]	3.81±0.08[.150±.003] DIA	5	213729-9
8 OBSOLETE	4.04[.159]	4-40UNC, INSERT, BRASS	6	213729-8
8 OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	6	213729-7
	9.35[.368]	4-40UNC, INSERT, BRASS	5	213729-6
7	4.04[.159]	3.81±0.08[.150±.003] DIA	4	213729-5
8 OBSOLETE	4.04[.159]	4-40UNC, INSERT, BRASS	4	213729-4
8 OBSOLETE	9.35[.368]	3.81±0.08[.150±.003] DIA	4	213729-3
8 OBSOLETE	9.35[.368]	4-40UNC, INSERT, BRASS	3	213729-2
	9.35[.368]	3.81±0.08[.150±.003] DIA	3	213729-1
	C	A	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. W.G.LENKER 12-3-91, R.STONE 12-11-91. APVD: R.STONE. NAME: RECEPTACLE ASSEMBLY, POSTED, SERIES 1, REVERSE SEX, CPC. PRODUCT SPEC: 108-10024. APPLICATION SPEC: 114-10004. SIZE: A1. CAGE CODE: 00779. DRAWING NO: 213729. WEIGHT: -. CUSTOMER DRAWING. SCALE: 2:1. SHEET: 1 OF 1. REV: G1.