



3) Threaded pin, 4) not included in scope of delivery, 5) Female, removable, 6) Allen key size 2

Basic features

Scope of delivery	Protective cap
Short description	Protective ring
Use	for inductive sensors BES M12

Environmental conditions

Ambient temperature	-50...650 °C
----------------------------	--------------

Material

Housing material	Stainless steel
Material	Stainless steel (1.4401)

Mechanical data

Clamping system	Screws
Diameter 2	12.00 mm
Dimension	Ø 19.05 x 8 mm
Installation	for flush mounting
Mounting	M12x1
Size	M12x1
Wall thickness t	3.5 mm