







3950X SERIES
3.50mm HEADERS




3952X & 3954X SERIES
5.00mm HEADERS
5.00mm 10 AMP FIXED




3953X SERIES
5.08mm HEADERS




3951X SERIES
3.81mm HEADERS



3954X SERIES
5.00mm 15 AMP FIXED



3954X SERIES
5.08mm 15 AMP FIXED



- NOTES:
1. REFER TO INDIVIDUAL PRODUCT SALES DRAWINGS FOR "B" DIMENSION.
 2. DOES NOT APPLY TO DUAL LEVEL HEADERS, SERIES 39528 AND 39538.
 3. TYP. = TYPICAL.


INITIAL RELEASE	EC NO: ETC2007-0096	2006/10/02
	DRWN: CLYORK	2006/10/04
	CHKD: JMACNEIL	2006/10/04
	APPR: JMACNEIL	2006/10/04
A		

QUALITY SYMBOLS
= 0
= 0
DESCRIPTION
REV

GENERAL TOLERANCES (UNLESS SPECIFIED)	
4 PLACES	$\pm .005$
3 PLACES	$\pm .01$
2 PLACES	$\pm .013$
1 PLACE	$\pm .03$
ANGULAR $\pm 2^\circ$	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
C. YORK	2006/08/25
CHECKED BY	DATE
J. MACNEIL	2006/08/25
APPROVED BY	DATE
J. MACNEIL	2006/08/25
MATERIAL NO.	
--	

SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
3:1	INCH		
TITLE			
RECOMMENDED PCB LAYOUT FOR ESE TERMINAL BLOCKS			
MOLEX INCORPORATED			
DOCUMENT NO.	SHEET NO.		
SD-39501-002	1 OF 1		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



SPECIFICATIONS:

- 1. Material:
 - (1). Body: PA66
 - (2). Pin: Brass
- 2. Wire range: N/A
- 3. Electrical rating: 300V, 15A.
- 4. Wire strip length: N/A
- 5. Operating temperature: -40C to +105C.
- 6. Max torque: N/A
- 7. Insulation resistance: DC 500V, 500M.
- 8. Dielectric withstand: AC 2500V for 1 minute.
- 9. Breakdown voltage: 4000V.
- 10. A = (N x P) + 2.0mm
- 11. B = (N - 1) x P
- 12. P (PITCH) = 5.08mm (.200").
- 13. N = Number of positions available 2 through 24.

ENTER DESCRIPTION EC NO: NEO2006-0310 DRAWN: LROTHAUS 2006/01/09 CHKD: CYORK 2006/01/09 APPR: JPAWLICK 2006/01/10 A			DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				▽=0			DRAWN BY LROTHAUS		DATE 12/6/05	TITLE 5.08MM, EURO HEADER, VERTICAL			
				◇=0			CHECKED BY C. YORK		DATE 01/06/06				
				1 PLACE ±0.3 ±---		APPROVED BY		DATE	MOLEX MOLEX INCORPORATED				
ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO. SD-39531-002				SHEET NO. 1 OF 1					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

